

Product data sheet

Specifications



Repacked, undervoltage release, Acti9, iMNx, 220VAC to 240VAC

A9A26969W



This repacked option saves 0.772 over the standard condition

Main

range of product	Acti9
Product or component type	Undervoltage release
Device short name	iMNx
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	With external feeding
9 mm pitches	2

Complementary

Range compatibility	Acti9 iC65 Acti9 ARA Acti9 iDPN Vig Acti9 iLD Acti9 iSW-NA Acti9 RCA double terminals miniature circuit breaker Acti9 iDPN (China version) Acti9 iC60 Acti9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 11 mm ² - rigid Clamp terminal - 2 cable(s) 2.1 mm ² - rigid Clamp terminal - 1 cable(s) 9 mm ² - flexible Clamp terminal - 2 cable(s) 2.1 mm ² - flexible with cable end
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.200 cm
Package 1 Width	7.300 cm
Package 1 Length	8.700 cm
Package 1 Weight	80.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	16
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.468 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.8 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

9da5f8d9-d60f-424a-bb30-a856a097686c

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins