

ZCE29

limit switch head ZCE - steel roller plunger with nitrile boot



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKP XCKD XCKT
Associated body	ZCT26G11 ZCD21 ZCD35 ZCT21N12 ZCMD21L5 ZCD27 ZCMD21C12 ZCMD37L2 ZCMD25L5 ZCMD21L08R12 ZCP37 ZCD29M12 ZCD25 ZCT21P16 ZCMD81L1 ZCT26N12 ZCT25G11 ZCMD41L1 ZCMD29C12 ZCP28 ZCP27 ZCMD39L5 ZCP35 ZCT28G11 ZCMD29L5 ZCT27P16 ZCMD25L1 ZCMD21L08U78

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD81L2
 ZCP26
 ZCP29
 ZCMD21L1
 ZCMD41L5
 ZCMD37L1
 ZCMD39L1
 ZCD31
 ZCT21G11
 ZCMD41L2
 ZCD28
 ZCMD21M12
 ZCMD25L2
 ZCMD29L2
 ZCD37
 ZCT27G11
 ZCD29
 ZCT26P16
 ZCMD21L2
 ZCMD37L5
 ZCT28P16
 ZCMD81L5
 ZCD21M12
 ZCP39
 ZCMD61C12
 ZCD39
 ZCT25P16
 ZCP25
 ZCMD69C12
 ZCMD61M12
 ZCP21
 ZCMD39L2
 ZCT25N12
 ZCP31
 ZCP21M12
 ZCP29M12
 ZCT28N12
 ZCD26
 ZCMD29L1
 ZCT27N12

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal (with nitrile boot)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------