

BH-V 252R

Pressed steel fixed castor, heavy duty design, with top plate fitting, wheel, with standard solid rubber tyre, with pressed steel rim, reinforced design

EAN 4047526062873

ID 62877

Customs tariff number 87169090



Bracket: BH series

- pressed steel, zinc-plated, blue-passivated, Cr6-free
- heavy fork and top plate

Wheel: V series

- tyre: standard solid rubber, hardness 80 Shore A, colour black
- rim: pressed steel, strong rim structure with tubular steel hub, bolted or pressed, zinc-plated, blue-passivated, Cr6-free

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, reduced load capacity over +60 °C
- Centrally-pressed version

Technical data:

Wheel Ø (D)	☉	250 mm
Wheel width	⊥	60 mm
Load capacity at 4 km/h	⚖	295 kg
Load capacity (static)	⚖	740 kg
Bearing type	⊙	roller bearing
Total height (H)	⊕	295 mm
Mounting type		top plate
Plate size	📏	140 x 110 mm
Bolt hole spacing	📏	105 x 75–80 mm
Bolt hole Ø	🔧	11 mm
Temperature resistance min		-25 °C
Temperature resistance max		70 °C
Tread and tyre hardness		80 Shore A
Unit weight	⚖	5.5 kg
Non-marking		×
Non-staining		×
Antistatic	⚡	×
ESD		×
Electrically conductive	⚡	×
Corrosion-resistant		×
Heat-resistant	🔥	×
Suitable for autoclaves		×
Suitable for machine washing		×



Tread and tyre hardness

■ ■ ■ ■ □ □ 80 Shore A

Rolling resistance


■ ■ □ □ □ □ satisfactory

Wear resistance

■ □ □ □ □ □ sufficient

Operating noise / floor surface preservation

■ ■ ■ ■ □ □ very good



Product references



Corresponding swivel castor L-V 252R-3



Wheel used V 252/25R