




RAST

TE Internal #: 3-1534797-3
Wire-to-Board, 13 Position, 2.5 mm [.098 in] Centerline, Insulation Displacement (IDC), 1 Row, Natural, PA 6 GF, Standard Edge Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**
Number of Positions: **13**
Centerline (Pitch): **2.5 mm [.098 in]**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**
Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	13
Number of Rows	1
Connector Contact Load Condition	Fully Loaded

PCB Mount Orientation: Right Angle

Electrical Characteristics

Operating Voltage	50 VAC, 250 VAC
-------------------	-----------------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features	
Contact Retention Within Housing	With
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Copper Tin Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Current Rating (Max)	2 A
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
PCB Mount Retention	Without
Contact Retention Type Within Housing	Locking Lance
Mating Retention	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	PA 6 GF
Dimensions	
Compatible Insulation Diameter Range	1.2 – 1.6 mm[.047 – .063 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Connector Height	7.3 mm[.287 in]
Wire Size	24 – 22 AWG
Usage Conditions	
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	



Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWEPT 750°C (Without Flame)

Packaging Features

Packaging Quantity	1078
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2406004-3
AMP DUOPLUG MK2 GWT V0 13P

TE Part # 2-2304526-3
13P DUOPLUG MK II GW-V0

TE Part # 3-1534796-4
AMP DUOPLUG MK2 CONNECTOR 4P S

TE Part # 1-2304526-3
13P DUOPLUG MK II GW-V0

TE Part # 2304526-3
13P DUOPLUG MK II GW-V0

TE Part # 2-2406004-3
13P DUOPLUG MK II GW-V0

TE Part # 3-1534796-7
AMP DUOPLUG MK2 CONNECTOR 7P

TE Part # 3-1534796-3
AMP DUOPLUG MK2 CONNECTOR 3P

TE Part # 4-1534797-3
AMP DUOPLUG MK2 CONNECTOR 13P GW-V2

TE Part # 3-1534797-2
AMP DUOPLUG MK2 CONNECTOR 12P

TE Part # 3-1534796-0
AMP DUOPLUG MK2 CONNECTOR 10P

TE Part # 3-1534797-4
AMP DUOPLUG MK2 CONNECTOR 14P

TE Part # 3-1534797-1
AMP DUOPLUG MK2 CONNECTOR 11P

TE Part # 3-1534796-5
AMP DUOPLUG MK2 CONNECTOR 5P

TE Part # 4-1534797-2
DUOPLUG MARK II CONNECTOR

TE Part # 9-1740154-3
DUOPLUG MKII FEMALE HSG WITH PCB LOCKING

TE Part # 9-1740154-6
DUOPLUG MKII FEMALE HSG WITH PCB LOCKING

Customers Also Bought



TE Part #1740533-5
AMP DUOPLUG POW CONN. 5POS
W.PCB LOCKING

TE Part #1-1740533-7
AMP DUOPLUG POW CONNECTOR

TE Part #4-1534797-2
DUOPLUG MARK II CONNECTOR

TE Part #5-1534798-9
AMP Duoplug 2,5 MK II selektiv

TE Part #1394918-6
DUOPLG5.0 BU-STE 6P

TE Part #1534415-8
DUOPL POW FEM CON8P

TE Part #2-1740533-4
AMP DUOPLUG POW CON 2-9 P
WITH PCB LOCKG

TE Part #3-1534796-0
AMP DUOPLUG MK2 CONNECTOR
10P

TE Part #3-1534797-4
AMP DUOPLUG MK2 CONNECTOR
14P

TE Part #3-966480-5
DUOPLUG2,5BUST11X5P

Documents

Product Drawings

AMP DUOPLUG MK2 CONNECTOR 13P

English

AMP DUOPLUG MK2 CONNECTOR 13P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1534797-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1534797-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1534797-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English

VDE Certificate

English