

Product data sheet

Specifications



Repacked, impulse relay, Acti9
iT⁺L⁺, 1P+N, 16A, 1 NO, 230VAC,
50Hz

A9C15032W



This repacked option saves 4.995 over the
standard condition

Main

range of product	Acti9
Product name	Acti9 iT ⁺ L ⁺
Product or component type	Impulse relay
Device short name	iT ⁺ L ⁺
Device application	Standard
Poles	1P + N
Neutral position	Left
Pole contact composition	1 NO
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	230 V AC 50 Hz

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz
Control type	Remote and manual control
Control signal type	Impulse
Switching frequency	6 switching operation/minute
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button 5 mA
Local signalling	ON/OFF indication
Hold-in power consumption in VA	1.1 VA
inrush power in VA	11 VA
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Product weight	70 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical durability	AC-21: 5000000 cycles AC-22: 5000000 cycles
Connections - terminals	Tunnel type terminals top or bottom 2 cable(s) 1.5 mm² rigid Tunnel type terminals top or bottom 2 cable(s) 1.5 mm² flexible with ferrule Tunnel type terminals top or bottom 2 cable(s) 2.5 mm² rigid Tunnel type terminals top or bottom 2 cable(s) 2.5 mm² flexible without cable end Tunnel type terminals top or bottom 1 cable(s) 4 mm² rigid Tunnel type terminals top or bottom 1 cable(s) 4 mm² flexible without cable end
Wire stripping length	10 mm
Tightening torque	1 N.m
Product compatibility	No auxiliary

Environment

Standards	EN 669-2-2
Quality labels	NF
Noise level	30 dB
IP degree of protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	7.1 cm
Package 1 Length	9.2 cm
Package 1 Weight	91.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	63
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.052 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins