






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		AD2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



WIRE SIZE #24-#20



INSULATION RANGE .069 MAX

- 1 GOLD PLATING IS NOT REQUIRED IN THIS AREA.
- 2 CUT-OUTS ON THE BOX ARE AT MANUFACTURERS OPTION.
- 3 THIS TERMINAL IS REELED FOR THE STANDARD APPLICATOR.
- 4 THIS TERMINAL IS REELED FOR THE MINI APPLICATOR.
- 5 .000030 GOLD OVER .000050 NICKEL.
- 6 .000030 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 7 PREPLATED:(HALT).000078-.000158 BRIGHT TIN
- 8 .000050 GOLD OVER .000050 NICKEL.
- 9 .000015 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 10 .000050 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 11 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 12 .000015 GOLD IN CONTACT AREA, .000050 NICKEL ON ENTIRE TERMINAL
- 13 OBSOLETE PART NUMBER.
- 14 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4	12	13 -7	2- 13 -0
3	12	13 -7	1-85969-9
3	10	13 -6	1- 13 -8
4	10	13 -6	1- 13 -7
4	8	86016-4	1-85969-0
4	7	86016-3	85969-9
4	6	86016-2	85969-8
4	5	86016-1	85969-7
4	9	86016-5	85969-6
3	9	86016-5	13 -5
3	8	86016-4	14 -85969-4
3	7	86016-3	13 -3
3	6	86016-2	85969-2
3	5	86016-1	85969-1

SUPERSEDED BY 85969-4

REMARKS	FINISH	LOOSE PIECE PART NUMBER	PART NUMBER
---------	--------	----------------------------------	----------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.D.RINGLEY 10DEC85	TE Connectivity			
DIMENSIONS: INCHES		CHK J.L.GESFORD 16DEC85				
		APVD J.L.GESFORD 16DEC85	NAME			
		PRODUCT SPEC	CONTACT, MOD IV, RECEPTACLE, CRIMP SNAP-IN			
		APPLICATION SPEC				
MATERIAL BERYLLIUM COPPER, .008 THICK		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=85969	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE 10:1				
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH SEE TABLE		SHEET 1 of 1				
		REV AD2				