

CHAMP

TE Internal #: 5917334-5

TE Internal Description: CHAMP 050-2 REC HDR ASSY V 36P

[View on TE.com >](#)

Connectors > D-Shaped Connectors

Number of Positions: **36**Connector & Housing Type: **Receptacle**Connector System: **Cable-to-Board**Connector Mounting Type: **Panel Mount**Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

Shell Material Configuration	Front Metal Shell
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	36
Number of Rows	4
PCB Mount Orientation	Vertical

Body Features

Shell Plating Material	Nickel over Copper
Primary Product Color	Black
Connector Profile	Standard

Contact Features

Shell Plating Material	12 µin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Shape & Form	Spring

Contact Current Rating (Max)	.5 A, 1 A
------------------------------	-----------

Contact Options	Installed
-----------------	-----------

Termination Features

Rectangular Termination Post & Tail Width	.4 mm[.015 in]
---	----------------

Rectangular Termination Post & Tail Thickness	.32 mm[.012 in]
---	-----------------

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Termination Post & Tail Length	3.1 mm[.122 in]
--------------------------------	-----------------

Mechanical Attachment

Mounting Hole Diameter	2.88 mm
------------------------	---------

Connector Mounting Type	Panel Mount
-------------------------	-------------

PCB Mount Retention	With
---------------------	------

PCB Mount Retention Type	Retention Leg
--------------------------	---------------

Mating Retention	With
------------------	------

Mating Retention Type	Latch
-----------------------	-------

Housing Features

Housing Material	Thermoplastic, Zinc Die Cast
------------------	------------------------------

Shell Material	Steel
----------------	-------

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Dimensions

Panel Thickness (Recommended)	2.01 mm[.079 in]
-------------------------------	------------------

PCB Thickness (Recommended)	1.6 mm[.063 in]
-----------------------------	-----------------

Row-to-Row Spacing	1.9 mm[.075 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	10
--------------------	----

Packaging Method	Tube
------------------	------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #ASA021N00210235000
623 PLUG




TE Part #900412-2
PC I/O RETENTION LEG ASSY 80P



TE Part #1123677-1
Z-STACK TYPE F16 ASSY 130P



TE Part #1473226-1
SOCKET WITH RING MINI U-M-N-L



TE Part #2-1586038-2
22P VRT HDR VAL-U-LOK V0



TE Part #2229093-1
MOD JACK ASSEMBLY V-TYPE H=21.7mm



TE Part #1-2271457-8
D3950 HDR 8POS 1ROW X KEY



TE Part #2309223-1
RITS CONN.HDR ASSY 4ROW 4P THR W TAPE



TE Part #5176371-4
VERT RCPT ASSY,100POS,CHAMP050



TE Part #1-5316316-0
.6FHP08H,140,S,GIG,08/Sn,HT,SEYes

Documents

Product Drawings

[CHAMP 050-2 REC HDR ASSY V 36P](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_5917334-5_O.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5917334-5_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5917334-5_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[CHAMP.050 Series\(II\) Connector Wire to Board Type](#)

English

Product Specification

English