



EXPERIENCE TO PERFORM

TECHNICAL DATA SHEET

FULCRON

Super degreasing cleaner Food Grade



Nonfood Compounds
Program Listed

PRODUCT FEATURES

FULCRON FOOD GRADE is a heavy-duty cleaner for every washable hard surface deputed to food processing. It will quickly remove dirt, grease and oil deposits; even the most difficult ones. Ideal for all types of cleaning applications. Does not contain any solvent, phosphates, EDTA or any caustic basis.

FULCRON FOOD GRADE is concentrated, you can dilute it even 1:100. Follow the list below to find the right concentration of use.

Suitable for HACCP plan use.

99.46% Biodegradable.

NSF A1 Nonfood Compounds Program Listed n.157857.

AREA OF USE (APPLICATIONS)

- Undiluted
Grids, cooker hoods, machineries.
- Diluted 1:5
Tiles and tile grouts.
- Diluted 1:20
Working surfaces, floors.
- Diluted 1:100
Windows and any glass parts

CHEMICAL AND PHYSICAL PROPERTIES

- | | |
|-------------------|-------------------------------|
| • Appearance | Liquid |
| • Color | Colorless |
| • Odor | Typical |
| • Density at 20°C | 1.03 – 1.05 g/cm ³ |
| • pH (20°C) | 11.5-12.5 |

The reported data are subject to normal manufacturing tolerances

DIRECTIONS FOR USE

Use the product at the recommended dilutions. Apply the product on the surfaces to clean. Wipe off with water or a wet sponge. Use of drinkable water is mandatory. If the dirt is difficult to remove scrub the surface with a brush and leave the product for a longer time (not more than 10 minutes).

PRECAUTIONS

On glass surfaces use the product only diluted 1:100. In case of accidental contact with the glass, rinse well and dry the surface immediately. Do not apply on hot surfaces.

SHELF LIFE

Minimum 3 years. Store tightly closed in the original container in a dry area at temperatures between 5 and 40°C. Avoid direct sunlight.

PACKAGING

Cod. 1981 5 L PE tank

Cod. 2031 500 mL trigger PE bottle

ADDITIONAL INFORMATION

For further information about product safety, please consult Safety Data Sheets.

T.S 02.04.2021

The data contained herein are the result of technological research by our laboratories and are given for informative purposes only. We exclude any liability deriving from the incorrect choice or application of the product and from the lack of the necessary precautions, which should be carefully checked by the user. For information, please contact our Technical Dept. on no. +39 02924361

AREXONS S.p.A. A SOCIO UNICO

Via Antica di Cassano, 23
20063 Cernusco sul Naviglio (MI) Italy
Capitale Sociale: €15.000.000,00 I.V.
Registro delle Imprese di Milano n. 09728360968
Codice Fiscale e Partita IVA 09728360968
Direzione e coordinamento ex art. 2497 c.c. PLI (Netherlands) B.V.
Centralino 02 92436.1
Fax 02 92436.306
www.arexons.com

A wholly-owned subsidiary of PETRONAS

Sistemi di gestione di qualità della società Arexons S.p.A.
certificati ISO 9001 da LRQA.

Sistemi di gestione di ambiente e sicurezza della società Arexons S.p.A.
certificati ISO 14001 e OHSAS 18001 da Bureau Veritas.

