




Part Number : [1200310027](#)
Product Description : Nano-Change (M8) Receptacle, 5 Poles, B-Coded, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length
Series Number : 120031
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : 4R5F06E02C3003




Documents & Resources

Drawings
[1200310027_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120031
Description	Nano-Change (M8) Receptacle, 5 Poles, B-Coded, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906177843

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	B-Coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Net Weight	10.100/g
Orientation	Straight

Panel Mount	Front
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	24

This document was generated on Mar 27, 2025