

SUPERBLAST

GREATER COMFORT AND PROTECTION

SUPERBLAST goggles gets softer frame, a PLATINUM® version and a simplified intuitive assembly system goggle-Visor.



113 g

OPTIONAL

Optical insert
SOSBLAST



VISOR ONLY



SUPBLAPSI



SUPBLEPSI



SUPBLFAPSI



SUPBLAPSIP 



SUPBLV



SUPFABLAPSIP 



SUPBLAWPCC5

**+ WITH OR WITHOUT FOAM
(ACCORDING TO VERSIONS)**

+ ALL-ROUND VISION

+ BALL-PIVOT

+ ADJUSTABLE STRAP

+ OVERFLOW CHUTE FOR LIQUIDS

**+ FITS OVER PRESCRIPTION
GLASSES**

**+ COMPATIBLE WITH
HALF-MASK RESPIRATOR**

bolle
SAFETY

SUPERBLAST

GREATER COMFORT AND PROTECTION

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
SUPERBLAST	Ventilated	SUPBLAPSI	2C-1,2 ☞ 1 9 BT C€	☞ EN166 3 4 9 BT C€	Anti-scratch/Anti-fog
	Sealed	SUPBLEPSI	2C-1,2 ☞ 1 9 BT C€	☞ EN166 3 4 5 9 BT C€	Anti-scratch/Anti-fog
	Ventilated frame Breathable foam	SUPBLFAPSI	2C-1,2 ☞ 1 9 BT C€	☞ EN166 3 4 9 BT C€	Anti-scratch/Anti-fog
	Ventilated	SUPBLAPSIP	2C-1,2 ☞ 1 9 BT KN C€	☞ EN166 3 4 9 BT C€	Anti-scratch/Anti-fog (☞P)
	Spare lens	SUPFABLAPSIP	2C-1,2 ☞ 1 9 BT KN C€	-	Anti-scratch/Anti-fog (☞P)
	Visor for SUPERBLAST only	SUPBLV	-	☞ EN166 3 BT C€	-
	Ventilated Welding shade 5	SUPBLAWPCC5	5 ☞ 1 9 BT C€	☞ EN166 3 4 9 B C€	Anti-scratch
	Optical insert	SOSBLAST	-	-	-

LENS MARKING

Optical class symbols:

1. Continuous work

Use symbols:

9. Molten metal and hot solids.

Mechanical strength symbols:

B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.

T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

Others symbols:

K. Resistance to surface damage by fine particles

N. Resistance to fogging (optional)

C€ European standard ☞ Manufacturer name

FRAME MARKING

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

3. Liquid droplets or splashes.

4. Large dust particles > 5 microns.

5. Gas and fine dust particles < 5 microns.

9. Molten metal and hot solids.

B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.

T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

C€ European standard ☞ Manufacturer name

Bollé Safety product approval certificates to CE standards will be sent on request.

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.



14/02/2017

Europe Bollé Safety
95 rue Louis Guérin
69100 Villeurbanne - France
Tél. : 00 33 (0) 4 78 85 23 64
Fax : 00 33 (0) 4 78 85 28 56
contact@bolle-safety.com

bolle-safety.com

U.K. Bollé Safety
Unit C83 - Barwell Business Park Leatherhead Road - Chessington
Surrey - KT9 2NY
Tél. : 00 44 (0)208 391 4700
Fax : 00 44 (0)208 391 4733
e-mail : sales@bolle-safety.co.uk

bolle
SAFETY

SUPERBLAST

GREATER COMFORT AND PROTECTION

CHARACTERISTICS

LENSES	PC - 2,0 mm
FRAME	PVC
TEMPLES	Non applicable
STRAP	Nylon
FOAM	ref. SUPBLFAPSI - SBR
SPARE LENSES	ref. SUPFABLAPSIP for SUPBLAPSIP

PACKAGING AND EAN 13 CODE

	SUPBLAPSI	SUPBLEPSI	SUPBLFAPSI	SUPBLAPSIP	SUPFABLAPSIP	SUPBLV	SUPBLAWPCC5	SOSBLAST
Individual plastic bag	3660740008161	3660740008178	3660740008185	3660740008192	3660740008208	3660740008215	3660740008222	3660740004804
5 safety goggles or 100 spare lenses	3660740108168	3660740108175	3660740108182	3660740108199	3660740108205	3660740108212	3660740108229	3660740104801
65 safety goggles or 600 spare lenses or 80 SUPBLV per outer pack	3660740208165	3660740208172	3660740208189	3660740208196	3660740208202	3660740208219	3660740208226	3660740204808



14/02/2017

Europe Bollé Safety
95 rue Louis Guérin
69100 Villeurbanne - France
Tél. : 00 33 (0) 4 78 85 23 64
Fax : 00 33 (0) 4 78 85 28 56
contact@bolle-safety.com

bolle-safety.com

U.K. Bollé Safety
Unit C83 - Barwell Business Park Leatherhead Road - Chessington
Surrey - KT9 2NY
Tél. : 00 44 (0)208 391 4700
Fax : 00 44 (0)208 391 4733
e-mail : sales@bolle-safety.co.uk

bolle
SAFETY