

Rail mountable BNC-Connector

Type of housing



Material = 6.6 polyamide, see page 14
color: gray

Marking material see page 322

Mounting material see page 344

Coax cables with BNC plugs are a world-wide accepted standard for high frequency signal transmissions in video cabling as well as industrial peripheries.

The new BNC connectors represent a rail mountable variation of this technology offering the interface characteristic of the modular terminal block for Coax cable installation







BNC-V

single level



BNC-DV

double level

Description	Type	Order No.	Pcs. Pkt.	Type	Order No.	Pcs. Pkt.
BNC-connector , single level, for mounting on  or  , with 50 Ω impedance	BNC-V 50	28 05 04 1	10			
BNC-connector , as above, however with 75 Ω impedance	BNC-V 75	28 05 07 0	10			
BNC-connector , double level, for mounting on  or  , with 50 Ω impedance				BNC-DV 50	28 05 03 8	10
BNC-connector , as above, however with 75 Ω impedance				BNC-DV 75	28 05 08 3	10

The important technical application advantages:

- single or double level,
- rail mountable in rows and
- individually markable

Especially in large systems, technically accurate and visually clean wiring, particularly with regard to an interface, is an important criteria. With the insulated rail mounting the danger of accidental contact with the coax shield and the ground is excluded. Due to the double level design an excellent density is obtained.

The BNC connector is available with impedances of 50 or 75 Ohm, which can clearly be distinguished by a corresponding imprint. For special designs in solder or cable crimp techniques, custom equipped plastic components.

For clear marking use the transparent label DST 22 with insert strips ES 22.

