

## MPP ix Type A - RJ45 IP20 Cat6A PVC 10m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 344 7805 100
Specification	MPP ix Type A - RJ45 IP20 Cat6A PVC 10m
HARTING eCatalogue	<a href="https://harting.com/33483447805100">https://harting.com/33483447805100</a>

### Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING Mini PushPull HARTING ix Industrial® Type A Overmoulded IDC termination
Connector 2	HARTING DualBoot RJ45 Piercing termination
Type of cable	Copper cable (round)

### Version

Cable length	10 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC insulation displacement termination Piercing termination

### Technical characteristics

Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz
------------------------------	--



Pushing Performance  
Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C unmoved
	-10 ... +70 °C moved
	-5 ... +70 °C During laying
Cable diameter	6.6 mm ± 0.3 mm

## Material properties

Material (cable)	PVC
Colour (cable)	Yellow

## Specifications and approvals

Specifications	UN/ECE-R 118
	UL 2556 Sec. 9.1 (FT2 Horizontal Flame Test)
	UL 1581 Sec. 1100 (FT2 Horizontal Flame Test)
	UL 1581 Sec. 1061 (CFT Cable Flame Test)
	IEC 60332-2-2 Flame retardancy

## Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140796607
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600