

MILWAUKEE TOOL

Milwaukee Electric Tool Corporation
BROOKFIELD, WI 53005
USA
Tel: +1 (262) 781-3600 • Fax: +1 (262) 790-6333

Milwaukee Asia Office
29/F, Tower 2, Kowloon Commerce Centre,
51 Kwai Cheong Road, Kwai Chung, Hong Kong
Tel: +852-2492-2181 • Fax: +852-2490-4778

Distributed by:

3/6/2021


All data incl. service and warranty conditions as well as product range are subject to change without notice.
Pictures not binding. No liability for printing errors or mistakes. © 2021 Milwaukee Electric Tool Corporation.
All trademarks are owned by Techtronic Cordless GP unless otherwise stated.


www.milwaukeetool.asia

Milwaukee™

M18 FUEL™

DRIVEN TO OUTPERFORM.™





POWERSTATE™ BRUSHLESS MOTOR



REDLINK PLUS™ INTELLIGENCE



REDLITHIUM™-ION BATTERY PACK

M18 CHS355
M18 FUEL 355MM ABRASIVE CHOP SAW

GENERATES **CORDED POWER**

RAPIDSTOP

CUTS UP TO **200** STEEL STUDS PER CHARGE

DRIVEN TO OUTPERFORM.

M18 FUEL is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL products feature three MILWAUKEE exclusive innovations - the POWERSTATE Brushless Motor, REDLITHIUM-ION Battery Pack and REDLINK PLUS Intelligence Hardware and Software - that deliver unmatched power, run-time and durability.


M18 FUEL

OVERLOAD INDICATOR LIGHT
Lights up when pushing too hard, coaching user to the optimal cutting speed

CARRY HANDLE
Easier Transportation

M18 REDLITHIUM-ION HB12 BATTERY
Delivers power while running cooler than our M18 REDLITHIUM-ION M18B5 batteries

TOOL-FREE ADJUSTABLE FENCE
Fast changes to cut smaller material and the ability to miter up to 45°



DUAL-ACTUATED TRIGGER
Limits accidental tool start ups

TOOL-FREE BLADE CHANGE
Faster and Easier blade Changes


ADJUSTABLE SPARK GUARD
Reduce number of sparks behind the cut

ENGRAVED MITER GAUGE
Easily adjust miter angle up to 45°

QUICK ADJUST VICE
Easily slide vice back to meet material before locking into place

M18 FUEL 355MM ABRASIVE CHOP SAW

GENERATES CORDED POWER



- Added portability with equivalent power for increased productivity

RAPIDSTOP



- Stops the disc in 3 seconds or less

RAPID STOP BRAKE



- Less down time and more productivity



SPECIFICATIONS

DESCRIPTION	SPECIFICATIONS	DESCRIPTION	SPECIFICATIONS
RPM	4,000	Maximum Cut Capacity (Round Material)	125 mm
Arbor Size	25.4 mm	Maximum Cut Capacity (Square Material)	100 mm
Cut-off Wheel Diameter	355 mm	Maximum Miter Capacity	45°
Blade Thickness	2.4 mm	Weight (w/ M18 HB12)	20.8 kg