



Figure similar

SIMATIC, electronic module for ET200iSP, 4 DO, 17.4 V DC/40 mA "H"-shutdown, Ex ib (ia Ga) IIC T4 Gb, Ex ib [ia IIIC Da] IIC T4 Gb, Ex ib [ia] I Mb

General information	
Product brand name	SIMATIC
Product family	ET 200iSP
Product category	Digital module output
Product type designation	4DQ 17.4 V DC/40 mA
HW functional status	2
Firmware version	V3.0.0
Product version	SHUT DOWN "H"
Installation type/mounting	
Rack mounting	No
Front mounting	Yes
Rail mounting	Yes
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	DC
Input current	
Current consumption, typ.	380 mA
from load voltage (power bus), max.	400 mA
Power loss	
Power loss, typ.	2.8 W
Address area	
Address space per module	
• Address space per module, max.	2 byte
Hardware configuration	
Fieldbus connection via separate transceiver	Yes
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	4; additionally 1 intrinsically-safe input for H shutdown
Short-circuit protection	Yes
No-load voltage U_{ao} (DC)	17.4 V
Internal resistor R_i	167 Ω
Trend key points E	
• Voltage U_e (DC)	10.7 V
• Current I_e	40 mA; 80 mA when outputs connected in parallel
Output voltage	
• Type of output voltage	DC
• permissible voltage at output, min.	0 V
• permissible voltage at output, max.	17.4 V

Output current	
• for signal "1" rated value	0.04 A
Output delay with resistive load	
• "0" to "1", max.	2 ms
• "1" to "0", max.	1.5 ms
Parallel switching of two outputs	
• for uprating	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
Cable length	
• shielded, max.	500 m
• unshielded, max.	500 m
Interfaces	
Number of PROFINET interfaces	0
Number of RS 485 interfaces	0
Protocols	
Supports protocol for PROFINET IO	No
PROFIsafe	No
PROFIBUS	No
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes; Parameterizable
• Hardware interrupt	No
Diagnoses	
• Diagnostic information readable	Yes
• Wire-break	Yes; $R > 10 \text{ kohms}$, $I < 100 \mu\text{A}$
• Short-circuit	Yes; $R < 80 \text{ Ohm}$ (one output), $R < 40 \text{ Ohm}$ (outputs connected in parallel)
Diagnostics indication LED	
• Group error SF (red)	Yes
• Status indicator digital output (green)	Yes; Per channel
Ex(i) characteristics	
Module for Ex(i) protection	Yes; for more Co/Lo combinations, see certificate IECEx KEM 05.0011
maximum values for connecting terminals for gas group IIC	
• U_o (no-load voltage), max.	19.4 V
• I_o (short-circuit current), max.	118 mA
• P_o (power output), max.	0.57 W
• C_o (permissible external capacity), max.	0.24 μF
• L_o (permissible external inductivity), max.	2.5 mH
• U_i (intrinsically safe input voltage), max.	28 V; switch input circuit
• P_i (intrinsically safe input power), max.	1.2 W; switch input circuit
• C_i (internal capacity), max.	3 nF; switch input circuit
Potential separation	
Potential separation digital outputs	
• between the channels	No
• between the channels and backplane bus	Yes
• Between the channels and load voltage L+	Yes
Permissible potential difference	
between different circuits	60 V DC/30 V AC
Degree and class of protection	
IP degree of protection	IP30
Standards, approvals, certificates	
CE mark	CE 0344
UKCA mark	DEKRA 21UKEX0085 Importer UK: Siemens plc Manchester M20 2UR
cULus	LISTED E334384
FM approval	CLASSIFIED 3025852
Suitable for safety functions	No
INMETRO certificate	UL-BR 12.0073

reference designation according to IEC 81346-2 (2009)	K																																										
Highest safety class achievable in safety mode																																											
SIL acc. to IEC 61508	No																																										
Use in hazardous areas																																											
ATEX marking	II 2 G (1) G Ex ib [ia Ga] IIC T4 Gb II 2 G (1) D Ex ib [ia IIIC Da] IIC T4 Gb I M2 Ex ib [ia] I Mb																																										
ATEX certificate	KEMA 04 ATEX 1249																																										
IECEX	IECEX KEM 05.0011																																										
CCC Ex	2020322316002945																																										
EAC Ex	PB Ex ib [ia] I Mb 1Ex ib [ia Ga] IIC T4 Gb [Ex ia Da] IIIC																																										
FM marking	Class I, Zone 1 AEx ib [ia] IIC T4 Ex ib IIC T4 NI, Class I, DIV.2, GP. A,B,C,D T4 AIS, Class I, DIV.1, GP. A,B,C,D T4 DIP Class II, III, GP. E,F,G																																										
Explosion protection category for gas	ATEX gas explosion protection, Zone 1																																										
Explosion protection category for dust	ATEX dust explosion protection, Zone 21 always install in corresponding enclosure																																										
associated equipment (Ex ia)	Yes																																										
associated equipment (Ex ib)	Yes																																										
Marine approval																																											
Germanischer Lloyd (GL)	Yes																																										
American Bureau of Shipping (ABS)	Yes																																										
Bureau Veritas (BV)	Yes																																										
Det Norske Veritas (DNV)	Yes																																										
Connection method																																											
Design of electrical connection	Screw/spring-type terminal																																										
Dimensions																																											
Width	30 mm																																										
Height	129 mm																																										
Depth	136.5 mm																																										
Weights																																											
Weight, approx.	255 g																																										
Classifications																																											
	<table><tr><td></td><td>Version</td><td>Classification</td></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr><tr><td>ETIM</td><td>9</td><td>EC001599</td></tr><tr><td>ETIM</td><td>8</td><td>EC001599</td></tr><tr><td>ETIM</td><td>7</td><td>EC001599</td></tr><tr><td>IDEA</td><td>4</td><td>3566</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-05</td></tr></table>		Version	Classification	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599	ETIM	9	EC001599	ETIM	8	EC001599	ETIM	7	EC001599	IDEA	4	3566	UNSPSC	15	32-15-17-05
	Version	Classification																																									
eClass	14	27-24-26-04																																									
eClass	12	27-24-26-04																																									
eClass	9.1	27-24-26-04																																									
eClass	9	27-24-26-04																																									
eClass	8	27-24-26-04																																									
eClass	7.1	27-24-26-04																																									
eClass	6	27-24-26-04																																									
ETIM	10	EC001599																																									
ETIM	9	EC001599																																									
ETIM	8	EC001599																																									
ETIM	7	EC001599																																									
IDEA	4	3566																																									
UNSPSC	15	32-15-17-05																																									
Approvals / Certificates																																											
General Product Approval																																											
																																											
Miscellaneous	China RoHS																																										
																																											
For use in hazardous locations																																											



[FM](#)



[Miscellaneous](#)



For use in hazardous locations	Maritime application
--------------------------------	----------------------

[CCC-Ex](#)



[Miscellaneous](#)

[Miscellaneous](#)



Maritime application	Environment
----------------------	-------------



[NK / Nippon Kaiji Ky-
okai](#)



last modified:

7/7/2025