




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Board, Wire-to-Wire**
Contact Retention Within Housing: **Without**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Multiple Contact Types	Without
Contact Layout	Matrix
Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Material	Nylon

Dimensions

Connector Width	13.97 mm[.549 in]
Connector Height	27.43 mm[1.08 in]
Connector Length	27.43 mm[1.079 in]
Row-to-Row Spacing	6.35 mm[.25 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

--



Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-350720-9
09P UMNL V0 PLUG HSG BLACK



TE Part # 2178773-1
UMNL 6 WAY CAP HOUSING



TE Part # 1586887-1
06P UMNL CAP HSG, P/M, GW



TE Part # 794536-1
06P UMNL CAP HSG 150C BLK



TE Part # 794714-3
06P UMNL CAP HSG RED,PAN MNT



TE Part # 770027-1
06P UMNLII IN-LINE CAP HSG KIT



TE Part # 770051-1
06P UMNL II CAP-FRONT 94VO



TE Part # 926682-3
06P UNIV.M-N-L.HSG.



TE Part # 1969881-1
06P UMNL CAP HSG, P/M, GW V0



TE Part # 1-480705-2
06P UNML CAP HSG RED



TE Part # 1586379-1
06P UMNL PLUG HSG NATL



TE Part # 1586860-1
06P UMNL CAP HSG, GW



TE Part # 8-794536-1
06P UMNL CAP HSG 150C BLK, SPE



TE Part # 643253-1
06P UMNL ASSY MOD HSG VO



TE Part # 794535-1
06P UMNL PLUG HSG 150C BLK



TE Part # 926682-4
6P UN-MNL AUFN-GEH



TE Part # 1-350720-4
09P UMNL V0 PLUG HSG YELLOW



TE Part # 1969779-1
6POS UMNL W/ INTERFACE & WIRE SEAL



TE Part # 1-480705-1
06P UMNL CAP HSG BRN



TE Part # 1-480705-9
06P UMNL CAP HSG BLK


Also in the Series | **Universal MATE-N-LOK**



Circular Power Connectors(2)



Connector Caps & Covers(34)



Connector Hardware(12)



Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(285)



Rectangular Power Connectors(643)



Wire-to-Board Headers & Receptacles (285)

Customers Also Bought




TE Part #M3021-000005-05KPG
PRESS XDCR M3021-000005-05KPG



TE Part #1586090-1
06P UMNL PINHDR NO DRAIN HOLE



TE Part #1586174-1
06P UMNL PIN HDR 94VO NDH



TE Part #1623795-7
SQP10 2R2 5% WIRE



TE Part #4-1879075-0
THS25 150R 5%



TE Part #9-1879350-9
RR01 5% 2K7 AMMO




TE Part #9-1879352-5
RR02 5% 2K7 AMMO



TE Part #1969814-1
06P UMNL PIN HDR ASSY, PIN V0 GW



TE Part #2344657-5
FPC ANTENNA, MHF4, 50mm, Wi-Fi TRIPLE



TE Part #M3031-000005-01KPG
PRESS XDCR M3031-000005-01KPG

Documents



Product Drawings

06P UMNL PLUG HSG 150C BLK, SP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-794535-1_C1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_8-794535-1_C1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-794535-1_C1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English