

Terxon PSTN Dialer

Art. no. AZ6301

Page 1 of 2



- TBR/CTR-21 compliant
- Alarm repetition
- Remote acknowledgement configurable
- Also usable as a standalone communication module
- Illuminated display

As soon as a detector triggers an alarm in your building, your alarm panel knows the current status. With the Terxon PSTN dialer, this information is passed on to up to four telephone numbers that are saved by you in the foreground. In the event of an alarm, the analog speech dialling unit transmits two pieces of information: an identification text and an event text. The identification text conveys general data (name, address) and the event text conveys events that are defined by you (break-in, fire, medical emergency, system fault, etc.). You can record and save four event texts of any kind. The texts have a total duration of 40 seconds. The analog speech dialling unit is installed between the alarm system and telephone line. It has four inputs, which activate the event text provided for this purpose in the event of an alarm. The call numbers are automatically dialled by the speech dialling unit. Thus, you can be certain that the recipients will be reliably notified. The dialling unit is programmed via a menu-driven LCD display. The analog speech dialling unit is approved throughout Europe and is a good visual fit for the Terxon alarm center due to its elegant white color.

Terxon PSTN Dialer

Art. no. AZ6301

Page 2 of 2

Technical Data:

Dimensions	(WxHxD) 150x115x30 mm
Connections	Screw terminal for PSTN and power supply
Number of voice messages	4
Display	Illuminated segment display
Type of inputs	Positive/negative controllable inputs (5-28 V DC)
Outputs	1 transistor output (OP), negative switching, max. current output 100 mA / 12 V DC per output
Width	150 mm
Inputs	4
Remote access	Yes
Housing material	ABS
Height	115 mm
Length	30 mm
Max. operating temperature	55 °C

Min. operating temperature	-10 °C
Net weight	0.36 kg
Configuration (1)	Menu
Tamper monitoring	Yes
IP protection class	32
Voltage monitoring	Yes
DC voltage supply	12 V
Power consumption	35 mA
Telephone number storage spaces	4
Transmission method	Language
Transmission path	PSTN