

- Dies and locator from this tool can be used in the Battery Powered Tool Order No. 63816-0200 (110 V) or 63816-0250 (220 V) with the use of the 63816-0800 Crimp Head
- Many different tool kits can be used with a single Battery Powered Crimp Tool
- This tool is IPC/WHMA A-620 Class 2 compliant (see Scope table)
- This tool is RoHS compliant; however, RoHS compliance is not required

## SCOPE

Revision: B

Products: Micro-Fit 3.0 Crimp Terminals, 0.75mm<sup>2</sup> and 18AWG (UL1061) wires.

Terminal	Terminal Order No.	Wire Size			Insulation	Stain Longeth			
Series No.				IPC/WHMA-A620 (1)		Termi	nal (2)	Strip Length	
		AWG	mm²	mm	ln.	mm	ln.	mm	ln.
43030	43030-0038								
43031	43031-0021	18	0.75	1.60-1.85	.063073	0.90-1.85	.035073	2.54-2.92	.100115
	43031-0022	10							
• (3)	43031-0023			1.00-1.00	.003073	0.90-1.00	.030073	2.04-2.92	.100115
45807	45807-0003	18	N/A						
40007	45807-0005	10	IN/A						
Insulation Diameter Notes									
(1) Insulation OD range for optimum (IPC/WHMA-A620 Class 2) insulation crimps									

(2) Insulation OD range for the terminal product design

Revision Date: 09-11-17

Terminal Locator Note

(3) Separate terminal locator is needed for 43031 series (see Page 2). If locator is missing it can be ordered (see Page 8)



# CONDITIONS

Terminal No.	Wire Size		Conductor Crimp Height		Conductor Crimp Width (Ref)		Pull Force Minimum		Tool Profile		Locator	
	AWG	mm <sup>2</sup>	mm	In.	mm	In.	Ν	Lb.	18	0.75mm <sup>2</sup>	Order No.	Color
43030-0038	18	N/A	1.00-1.10	0.039-0.043		0.065	89	20	Х		63828-0275	Red
	N/A	0.75	0.85-0.95	0.033-0.037						Х		
43031-0021	18	N/A	1.00-1.10	0.039-0.043	1.65				Х		63828-0276	Yellow
	N/A	0.75	0.85-0.95	0.033-0.037						Х		
43031-0022	18	N/A	1.00-1.10	0.039-0.043					Х			
	N/A	0.75	0.85-0.95	0.033-0.037						Х		
43031-0023	18	N/A	1.00-1.10	0.039-0.043					Х			
	N/A	0.75	0.85-0.95	0.033-0.037						Х		
45807-0003 45807-0005	18	N/A	1.00-1.10	0.039-0.043	1.65	0.065	89	20	Х		63828-0275	Red

After crimping to the wire, the crimped terminal should measure as follows:

Terminal Series	Wire	Size	Insulatio Heigh	on Crimp t (Ref)	Insulation Crimp Width (Ref)		
Series	AWG	mm <sup>2</sup>	mm	In.	mm	ln.	
43030							
43031	18	0.75	1.90	.075	2.00	.078	
45807							

#### **Tool Qualification Notes**

- 1. (Ref) means the dimension provided is approximate due to the wide range of wires, conductor stranding, insulation diameter, and insulation hardness.
- 2. An occasional pull force test should be performed. It must exceed the minimum pull force specification.
- 3. Pull force should be measured with no influence from the insulation crimp. To ensure this, strip the wire long enough so the terminal insulation grips do not contact the wire insulation.

# OPERATION

**CAUTION:** Crimp only the Molex terminals listed in the scope for this tool. Do not crimp hardened objects because damage can occur to the tool frame or crimp dies.

Open the tool by squeezing the handles together. At the end of the closing stroke, the ratchet mechanism will release the handles and the hand tool will spring open. See Figure 1.

#### **Crimping Terminals**

1. Select the desired terminal listed in the preceding charts.



- 2. Make sure the center of the locator is in the down position. With the locator attached, push the locator button on the back of the hand tool to bring the locator forward through the tooling. See Figure 2.
- 3. While holding the locator button in, load the terminal into the proper nest opening in the locator based on the wire gauge or terminal type markings on the hand tooling. See Figure 3.



- 6. Insert the properly stripped wire through the terminal and against the wire stop. See Figure 5.
- 7. Crimp the terminal by squeezing the tool handles until the ratchet mechanism cycle has been completed. Release the handles to open the jaws.



Note: The tamper-proof ratchet action will not release the tool until it has been fully closed.

- 8. Remove the crimped terminal from the terminal locator by pulling on the wire.
- 9. Visually inspect the crimped terminal for proper crimp location.
- 10. On some large O.D. wires, it may not be possible to insert the wire with the tool partially closed. Those wires should be inserted with the hand tool in the open position. Insert the wire above the terminal in the punch and against the wire stop, and then close the tool. See Figure 6.



Figure 6

## Locator Installation

Depending on the terminal to be crimped, the locator may need to be changed. Follow the steps below to remove and install the locator:

- 1. Open the crimp hand tool.
- Squeeze gently on the lower area shown in Figure 7A with your thumb and index finger. The lower tabs of the locator should disengage from the hand tool.
- 3. Lift and pull away from the hand tool. The top locator hooks should slip out of the top slots easily. See Figure 7A.
- 4. To reinstall the new locator, make sure the hand tool is in the open position.
- 5. Press the red insert down as far as it will go as shown in Figure 7B.
- 6. Holding onto the lower part of the locator with your thumb and index finger, insert the locator's top hooks (2) into the hand tool top slots.
- Rotate the locator down and press the lower tabs into the two bottom slots of the hand tool. To secure the locator into place, the lower tabs must snap into place on the hand tool frame.

# **Right or Left Hand Operation**

This hand tool has an added feature in that it can be converted from a right-handed application to a lefthanded application. It is necessary to reverse the tooling if using the left-handed application along with the locator. Follow the steps below:

- 1. The locator must be removed before reversing the tooling.
- 2. Remove the M3 BHCS, which is holding the upper tooling.
- Flip the upper tooling to the opposite side and replace the M3 BHCS. Make sure the small markings on the front and back of the hand tool frame match up and are on the outside of the hand tool frame. See Figures 8 and 9.
- 4. Do the same thing with the lower tooling and tighten the M3 screws. Be sure the small markings line up.
- 5. Reinstall the locator by following the instructions in the locator replacement section.



### Maintenance

It is recommended that each operator of the tool be made aware of and responsible for the following maintenance steps:

- 1. Remove dust, moisture and other contaminants with a clean brush or a soft, lint-free cloth.
- 2. Do not use any abrasive materials that could damage the tool.
- 3. Make certain all pins, pivot points and bearing surfaces are protected with a thin coat of high-quality machine oil. Do not oil excessively. The tool was engineered for durability, but like any other equipment, it needs cleaning and lubrication for a maximum service life of trouble-free crimping. Light oil (such as 30 weight automotive oil) used at the oil points every 5,000 crimps or 3 months will significantly enhance the tool life.
- 4. Wipe excess oil from hand tool, particularly from crimping area. Oil transferred from the crimping area onto certain terminations may affect the electrical characteristics of an application.
- 5. When the tool is not in use, keep the handles closed to prevent objects from becoming lodged in the crimping dies, and store the tool in a clean, dry area.

#### **Miscrimps or Jams**

Should this tool ever become stuck or jammed in a partially closed position, Do Not force the handles open or closed. The tool will open easily by pressing up on the ratchet release lever in the movable handle. See Figure 11.

## How to Adjust Tool Preload (See Figure 12)

This hand tool is factory preset to 25-45 pounds. preload. It may be necessary over the life of the tool to adjust tool handle preload force. Listed below are the steps required to adjust the crimping force of the hand tool to obtain proper crimp conditions:

1. Hold the hand tool in the palm of your hand as shown in Figure 10. Using your index finger, squeeze the link toward the top of the hand tool frame. This will release the preload adjustment wheel.



Release Date: 03-15-16 Revision Date: 09-11-17 UNCONTROLLED COPY

- 2. Rotate the setting wheel counterclockwise (CCW) to increase handle force. The numbers will display higher. To decrease handle force, rotate the setting wheel clockwise (CW).
- 3. Release the link to lock the setting wheel in place.
- 4. Check the crimp specifications or conduct a pull test after tool handle preload force is adjusted.

### Warranty

This tool is for electrical terminal crimping purposes only. This tool is made of the best quality materials. All vital components are long-life tested. All tools are warranted to be free of manufacturing defects for a period of 30 days. Should such a defect occur, Molex will repair or exchange the tool free of charge. This repair or exchange will not be applicable to altered, misused or damaged tools. This tool is designed for hand use only. Any clamping, fixturing or use of handle extensions voids this warranty.

CAUTION: Molex crimp specifications are valid only when used with Molex terminals and tooling.

### CAUTIONS:

- 1. Manually powered hand tools are intended for low-volume use or field repair. This tool is NOT intended for production use. Repetitive use of this tool should be avoided.
- 2. Insulated rubber handles are not protection against electrical shock.
- 3. Wear eye protection at all times.
- 4. Use only the Molex terminals specified for crimping with this tool.

#### Certification

Molex does not certify or re-certify hand tools but rather supplies the following guidelines for customers to re-certify hand tools:

- % This tool is qualified to pull force only. To re-certify, crimp a terminal to a wire that has been stripped 12.7mm (1/2") long so that there is no crimping of the insulation. Pull the terminal and wire at a rate no faster than 25mm (1.00") per minute. See the Molex website for the Quality Crimp Handbook for more information on pull testing.
- % If the tool does not meet minimum pull force values, handle preload should be increased and the pull test should be rerun (See How to Adjust Preload).
- % When the hand tool is no longer capable of achieving minimum pull force, it should be taken out of service and replaced.

# PARTS LIST

Item Number	Order Number	Description	Quantity	
REF	63828-0200	Hand Crimp Tool	Figure 13	
1	63828-0275	Locator Assembly (Red)	1	
1	63828-0276	Locator Assembly (Yellow)	1	
2	63810-0104	Spring, Return	1	
3	63810-0105	Spring, Ratchet	1	



Figure 13

#### **Application Tooling Support**

Phone: (402) 458-TOOL (8665) E-Mail: applicationtooling@molex.com Website: www.molex.com/applicationtooling

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

Release Date: 03-15-16 Revision Date: 09-11-17 **UNCONTROLLED COPY**