


KERN KFP 600V20SNM

KERN

Weighing bridge made from steel, also with weighing plate screwed on from the top



Category

Brand	KERN
Product category	Component
Product group	Weighing bridge
Product family	KFP-V20-IP67

Measuring System

Weighing capacity [Max]	600 kg
Readability [d]	200 g
Minimum weight [Min]	4 kg
Load cell connection	4-wire
Loadcell type	ZEMIC H8C 0.5 ton

Construction

Dimensions weighing surface (W×D)	1000×1000 mm
Dimensions weighing surface	1000×1000 mm
Dimensions weighing platform (W×D×H)	1000×1000×85 mm
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Material load cell(s)	alloyed steel
Levelling feet adjustable	✓
Cable length	5 m
Allowed cable length display device [Max]	20 m
Platform Construction	Screwed load plate; smooth surface
Load cells - number	4

Functions

IP protection - load cell	IP67
---------------------------	------

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Approval

Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	200 g

Services (optional)

Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1110×1065×350 mm
Shipping method	Freight
Net weight approx.	100 kg
Gross weight approx.	130 kg
Shipping weight	128 kg

Product information

GTIN/EAN number	4045761185166
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

