




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 2

Primary Product Color: **Yellow**

Protection & Strain Relief Accessory Type: **Cover - Cable Exit**

Primary Product Material: **PBT**

Strain Relief: **Without**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover - Cable Exit

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Yellow
Primary Product Material	PBT

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	5.7 mm[.224 in]
--	-----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
------------------	-----



Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 353746-1
SQUIB AIRBAG /FERRITE



TE Part # 353744-7
SQUIB AIRBAG/HSG-MAIN

Also in the Series | AMP Auto Squib Products



Automotive Connector Caps & Covers (2)	Automotive Connector Locks & Position Assurance(5)	Automotive Headers(1)	Automotive Housings(12)
Connector Contacts(1)	Other Automotive Connector Accessories(19)	PCB Headers & Receptacles(1)	Power Contacts(1)

Customers Also Bought

TE Part #353376-3 SQUIB CONT 1MM PIN DIA SOCKET	TE Part #1746872-1 0.64III 12POS PLUG ASSY	TE Part #353746-1 SQUIB AIRBAG /FERRITE	TE Part #CAT-M9194-T273 MULTILOCK, RECEPTACLE AND TAB
TE Part #353744-1 FIX-IN SQUIB CONN HSG-MAIN BK	TE Part #1612121-4 SQUIB 2POS PLUG HSG	TE Part #353744-7 SQUIB AIRBAG/HSG-MAIN	TE Part #1612124-8 1DIA SOCKET AU
TE Part #1827120-1 SQUIB LOCKING BUTTON			

Documents



Product Drawings

SQUIB AIRBAG/HSG-LID

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_353745-7_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_353745-7_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_353745-7_A1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English