




---

 PRODUCT-DETAILS

## SH202-D6

### Miniature Circuit Breaker - SH200 - 2P - 6 A - D - (AC) 6 kA




---

**General Information**

Extended Product Type	SH202-D6
Product ID	2CDS212001R0061
EAN	4016779699884
Catalog Description	Miniature Circuit Breaker - SH200 - 2P - 6 A - D - (AC) 6 kA
Long Description	SH202-D6 Miniature Circuit Breaker - 2P - D - 6 A

---

**ABB EcoSolutions**

ABB EcoSolutions	Yes
EcoSolutions Profile	9AKK108471A1003
Recyclability Rate of the Product acc. to EN45555	Design for Closing Resource Loops - Standard EN45555 - 92.1 %
ABB Site Meeting Group Waste To Landfill Target	No non-hazardous waste is sent to a landfill
Extended Product Lifetime	Product Durability
End Of Life Disassembling Instructions	9AKK108468A3121

Environmental Product  
Declaration - EPD

9AKK108468A1580

**Technical**

Dielectric Test Voltage	50 / 60 Hz - 1 min 2 kV
Power Supply Connection	Arbitrary
Contact Position Indication	ON / OFF
Energy Limiting Class	3
Electrical Endurance	20000 AC cycle
Mechanical Endurance	20000 cycle
Number of Protected Poles	2
Number of Poles	2P
Tightening Torque	2 N·m
Actuator Type	Toggle
Screw Terminal Type	Cage Terminal
Actuator Marking	I / O
Actuator Material	Insulation Group II, Black, Sealable
Recommended Screw Driver	Pozidriv 2
Accessories Available	No
Connecting Capacity	Conductor 25 / 25 mm <sup>2</sup> Flexible with Ferrule 0.75 ... 16 mm <sup>2</sup> Flexible 0.75 ... 16 mm <sup>2</sup> Rigid 0.75 ... 25 mm <sup>2</sup> Stranded 0.75 ... 25 mm <sup>2</sup>
Installation Size	acc. to DIN 43880 1
Terminal Type	Screw Terminals

**Electrical**

Tripping Characteristic	D
Rated Operational Voltage	acc. to IEC 60898-1 400 V
Operational Voltage	Maximum (Incl. Tolerance) 440 V AC Minimum 12 V AC
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC/EN 60664-1 440 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	4 kV at 2000 m 5 kV at Sea Level 6.2 kV
Input Voltage Type	AC
Rated Current (I <sub>n</sub> )	6 A
Rated Short-Circuit Capacity	(AC) 6 kA (400 V AC) 6 kA (400 V) 6 kA
Rated Conditional Short-Circuit Current (I <sub>nc</sub> )	(230 V) 6 kA (400 V) 6 kA
Rated Frequency (f)	50 / 60 Hz
Power Loss	3.8 W at Rated Operating Conditions per Pole 1.9 W
Overvoltage Category	III

## Design

Housing Material	Insulation Group II, RAL 7035
------------------	-------------------------------

## Material Compliance

RoHS Declaration	9AKK108472A0372
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	20251203
REACH Declaration	9AKK107492A1906
REACH Information	False - does not contain substances > 0.1 mass percentage
REACH Date	20251029
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
Toxic Substances Control Act - TSCA	9AKK108468A8104
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Reference Ambient Air Temperature	30 °C
Degree of Protection	IP20 Enclosure with Cover IP40
Pollution Degree	2
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Resistance to Vibrations	20 Cycles with Load 0.8 In: 5g 5 ... 150 ... 5 Hz
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms
Environmental Information	2CDK400030D0201

## Dimensions

Width in Number of Modular Spacings	2.0
Product Net Width	35 mm
Product Net Height	88 mm
Product Net Depth / Length	69 mm
Product Net Weight	0.204 kg
Pole Net Weight	0.125 kg
Built-In Depth (t <sub>2</sub> )	69 mm

## Ordering

Package Level 1 Units	carton 5 piece
Package Level 1 Gross Weight	1.06 kg

---

## Certificates and Declarations

---

Declaration of Conformity - CE	2CDK400607D2703
--------------------------------	-----------------

---



---

## Installation

---

Instructions and Manuals	2CDS207105P0001
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position	any

---



---

## Popular Downloads

---

Data Sheet, Technical Information	2CSC400030D0202
-----------------------------------	-----------------

---



---

## External Classifications and Standards

---

ETIM 9	EC000042 - Miniature circuit breaker (MCB)
ETIM 10	EC000042 - Miniature circuit breaker (MCB)
UNSPSC	39121603
eClass	V11.0 : 27141901
IDEA Granular Category Code (IGCC)	4897 >> Miniature circuit breakers
Standards	IEC/EN 60898-1
Certification Agency	EN IEC

---



---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs → Miniature Circuit Breakers MCBs → SH200

