

Description

CONDUCTIVE CASTOR WITH BOLT HOLE, GREY RUBBER 125MM

Part Number


Swivel
DP30A125-272L



Swivel and brake
DP30D125-272L



	Swivel	Swivel+brake
Wheel Diameter ØD	125 mm	
Overall Height H	159 mm ±1	
Fixing Hole Size	12 mm±1	
Center Hole	12,2 mm±0,3	
Offset F ±1	\	35 mm
Width of Tread	29 m±0,5	
Hardness of tread	shore A ± 93	
Load capacity	80 Kg	
Weight	0,54 kg	0,58 kg
Temperature	- 5 / + 50 °C	



Castor Assembly :

Zinc-plated steel. Swivel on two rows of balls.
Fastening by bolt hole.
Total lock. Plastic pedal.

Wheel :

Light grey polypropylene Wheel centre made from electroconductive materials.
Tread : Dark grey Thermoplastic tyre made from electroconductive materials.
Plain bearing.

Features :

Low starting effort,
Bonded Rubber,
Protects sensitive goods and users from electric shocks (electrostatic discharges).
Conductive casters compliant with ISO 22877.
Electrical resistance < 100000 ohms.
For use on trolleys or sensitive devices in laboratories, medical units, hospitals, electrical and electronic factories, explosion hazard areas....