


Geberit Mapress Stainless Steel ball valve with actuator lever



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For treated water (application range according to Technical Information „Treated water“)
- For rainwater with a pH value ≥ 5.5

CHARACTERISTICS

- Approval in accordance with DVGW
- Model Geberit T4

- Ball and base unit fully exposed to flow
- Lever fastening with screw
- Replaceable upper part
- Ball made of PPSU
- Upper part caulk made of EPDM
- Ball caulks made of silicone
- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature	-20 – +95 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

SCOPE OF DELIVERY

- Colour markings (red, blue, green)

INFO

- The ball valves are marked with PN 10 on the body in accordance with DVGW and EN 13828
- The ball valves are approved for up to PN 16

Art. no.	DNV	DN	d, ø mm	L cm	L1 cm	L2 cm	Z cm	PN bar
94952	15	12	15	10.4	5.9	9.2	3.2	16
94953	15	15	18	10.4	5.9	9.2	3.2	16

<i>Art. no.</i>	<i>DNV</i>	<i>DN</i>	<i>d, ø</i> <i>mm</i>	<i>L</i> <i>cm</i>	<i>L1</i> <i>cm</i>	<i>L2</i> <i>cm</i>	<i>Z</i> <i>cm</i>	<i>PN</i> <i>bar</i>
94954	20	20	22	11.6	6.2	9.2	3.7	16
94955	25	25	28	13.4	7.1	12.4	4.4	16
94956	32	32	35	15.4	7.6	12.4	5.1	16
94957	40	40	42	17.7	8.3	14.7	5.9	16
94958	50	50	54	20.6	9	14.7	6.8	16