

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight cable plug (male)

11_SHV-50-4-10/133_N

Properties

- Suitable for all high voltage applications up to 5 kV DC or 3.5 kV rms
- Used in nuclear instruments or test and measurement equipment
- Voltages are valid for both, the mated and the unmated condition.

**Product configuration**

Gender	Standard
plug	IEC 60498_MIL-STD-348A/314

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	0.3 GHz

Mechanical data

Weight	0.0223 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	clamped

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SHV, 50 Ohm, Straight cable plug (male)

11_SHV-50-4-10/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22541996	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22541996	11_SHV-50-4-10/133_NE	Single

Suitable cables	
Cable group	X16 - 4 mm / 75 Ohm --- obsolete (integrated in U18) U16 - 4 mm / 75 Ohm
Suitable cables	RG_59_B/U GX_04273

Additional Information	
Remarks	High voltage connector Working voltage (at sea level) 3.5 kV rms, 50Hz (depending on cable)
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543111	74_Z-0-0-1	Spanner

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3498 / Date of publication: 12.07.2025 / uncontrolled copy