



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1393143-1
27E043=SOCKET,KU,11,SLG,NYL,N



TE Part # 1393143-5
27E121=SOCKET,KUP,11,SCW,SURF-MOUNT



TE Part # 3-1393143-8
27E396=SOCKET,KU,11,SNAP,.187QC



TE Part # 1419106-4
27E046=SOCKET,KU,11,PCB,NYL,NAT



TE Part # 2-1419106-5
27E893=SOCKET,KU,11,QC,POLY,DINRAIL




TE Part # 1393143-2
27E067=SOCKET,KU,11,QC.187,NY,HARD-MNT

Also in the Series | **Potter & Brumfield KUL**




AC Relays(2)



DC Relays(2)



Electromechanical Relays(4)




Plug-In Relays(4)

Customers Also Bought



TE Part #1717138-5
025/040 SEALED 44POS PLUG ASSY



TE Part #1123343-2
025 REC CONTACT GOLD FORMING




TE Part #CAT-D485-W416
DEUTSCH DTM Wedgelocks



TE Part #DT06-08SA-E008
PLG, 8P, GRY, N, XCAP, A



TE Part #2-1630024-4
HSC250 4R7 5%



TE Part #282081-1
RUBBER PLUG



TE Part #2373965-1
CPA,AMPSEAL



TE Part #2411-002-1805
PANEL NUT, SIZE 18, HDP



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393116-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393116-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393116-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KUL 10 Amp Magnetic Latching Relay

English

KU Sockets & Accessories

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English