



SIMATIC S7-1200 G2, SB 1231 RTD, AI 2x 16-bit RTD, Pt100 and Pt1000

General information	
Product type designation	SB 1231, AI 2x 16-bit RTD
Input current	
from backplane bus 5 V DC, typ.	20 mA
Power loss	
Power loss, typ.	0.1 W
Analog inputs	
Number of analog inputs	2; Resistance thermometer
permissible input voltage for voltage input (destruction limit), max.	±35 V
Technical unit for temperature measurement adjustable	Degrees Celsius/degrees Fahrenheit
Input ranges	
• Voltage	No
• Current	No
• Thermocouple	No
• Resistance thermometer	Yes; Resistance-type transmitter: Pt10, Pt50, Pt100, Pt200, Pt500, Pt1000, Ni100, Ni120, Ni200, Ni500, Ni1000, Cu10, Cu50, Cu100, LG-Ni1000
• Resistance	Yes; 150 Ω, 300 Ω, 600 Ω
Input ranges (rated values), resistance thermometer	
• Cu 10	Yes
— Input resistance (Cu 10)	10 Ω
• Ni 100	Yes
— Input resistance (Ni 100)	100 Ω
• Ni 1000	Yes
— Input resistance (Ni 1000)	1 000 Ω
• LG-Ni 1000	Yes
— Input resistance (LG-Ni 1000)	1 000 Ω
• Ni 120	Yes
— Input resistance (Ni 120)	120 Ω
• Ni 200	Yes
— Input resistance (Ni 200)	200 Ω
• Ni 500	Yes
— Input resistance (Ni 500)	500 Ω
• Pt 100	Yes
— Input resistance (Pt 100)	100 Ω
• Pt 1000	Yes
— Input resistance (Pt 1000)	1 000 Ω
• Pt 200	Yes
— Input resistance (Pt 200)	200 Ω
• Pt 500	Yes
— Input resistance (Pt 500)	500 Ω

Input ranges (rated values), resistors	
• 0 to 150 ohms	Yes
• 0 to 300 ohms	Yes
• 0 to 600 ohms	Yes
Cable length	
• shielded, max.	100 m; to the sensor
Analog value generation for the inputs	
Measurement principle	integrating
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	15 bit; + sign
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	85 dB at 10 / 50 / 60 / 400 Hz
Smoothing of measured values	
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
Errors/accuracies	
Temperature error (relative to input range), (+/-)	25 °C ±0.1 % / -20 °C to 60 °C ±0.2 % of the full-scale deflection
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Common mode interference, min.	120 dB
Interrupts/diagnostics/status information	
Alarms	Yes
Diagnostics function	Yes; Can be read out
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Wire-break	Yes
Diagnostics indication LED	
• DIAG LED	Yes
• for status of the inputs	Yes
Isolation	
Isolation tested with	707 V DC (type test)
tested with	
• Between channels	120 V AC
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	No
UL approval	Yes
cULus	Yes
FM approval	No
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	No
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C; at max. voltages and max. specification
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C; at max. voltages and max. specification
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C

Air pressure acc. to IEC 60068-2-13	
• Operation, min.	540 hPa
• Operation, max.	1 140 hPa
• Storage/transport, min.	540 hPa
• Storage/transport, max.	1 140 hPa
Altitude during operation relating to sea level	
• Installation altitude, min.	-1 000 m
• Installation altitude, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Relative humidity	
• Operation, max.	95 %; no condensation
Vibrations	
• Vibration resistance during operation acc. to IEC 60068-2-6	3.5 mm from 5 - 8.4 Hz, 1g from 8.4 - 150 Hz
• Operation, tested according to IEC 60068-2-6	Yes
Shock testing	
• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27; half-sine, 15 g, 11 ms
Pollutant concentrations	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60 % condensation-free
connection method	
required front connector	Yes
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	
Width	15 mm
Height	62 mm
Depth	63 mm
Weights	
Weight, approx.	29 g
Classifications	

	Version	Classification
eClass	14	27-24-22-01
eClass	12	27-24-22-01
eClass	9.1	27-24-22-01
eClass	9	27-24-22-01
eClass	8	27-24-22-01
eClass	7.1	27-24-22-01
eClass	6	27-24-22-01
ETIM	9	EC001420
ETIM	8	EC001420
ETIM	7	EC001420

Approvals / Certificates		
General Product Approval		EMV

[Manufacturer Declaration](#)

[Miscellaneous](#)

[KC](#)



[KC](#)

last modified:

7/9/2025