


ディップシリーズ

TBシリーズ

標準在庫品




- ・ディップ外装ラジアルリード標準品
- ・静電容量：0.1 μ F~330 μ F
- ・静電容量許容差： $\pm 10\%$ (K)、 $\pm 20\%$ (M)
- ・定格電圧範囲：3.15V DC~50V DC

■定格別ケースサイズ表

W(V) Cap(μ F)	6.3	10	16	20	25	35	50
0.1						A	B
0.15						A	B
0.22						B	B
0.33						B	C
0.47					B	B	D
0.68				B	B	B	E
1.0			A	B	B	C	F
1.5			B	B	B	D	H
2.2		B	B	C	C	E	J
3.3	B	B	C	D	D	G	L
4.7	B	C	D	E	E	H	L
6.8	C	D	E	F	G	I	M
10	D	E	G	H	I	J	N
15	E	F	I	J	J	L	
22	F	H	J	K	L	M	
33	H	I	K	L	M	N	
47	I	K	L	M	N	N	
68	K	L	M	N	N		
100	L	M	N	P			
150	M	N	P				
220	N	P					
330	P						

TDシリーズ

受注生産品



- ・ディップ外装ラジアルリード小型品
- ・静電容量：0.1 μ F~100 μ F
- ・定格電圧範囲：4.0V DC~35V DC
- ・静電容量許容差： $\pm 10\%$ (K)、 $\pm 20\%$ (M)
- ・定格電圧範囲：3.15V DC~35V DC

■定格別ケースサイズ表

W(V) Cap(μ F)	6.3	10	16	20	25	35	50
0.1						A	
0.15						A	
0.22						A	
0.33				A	A	B	
0.47			A	B	B	B	
0.68			A	B	B	C	
1.0		A	A	C	C	D	
1.5	A	A	B	D	D	E	
2.2	A	B	C	E	E	F	
3.3	B	C	D	E	E	G	
4.7	C	D	E	G	G	H	
6.8	D	E	F	H	H	I	
10	E	F	G	I	I		
15	G	H	H				
22	G	H	I				
33	H	I	J				
47	I	J					
68	J						
100							

データシート

■TBデップシリーズ／標準品在庫シリーズ

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品名	tan (%)	L.C (μ A)
6.3	3.3	B	TBM0J335BSCB	6	0.50
6.3	4.7	B	TBM0J475BSCB	6	0.50
6.3	4.7	B	TBM0J475BSDB	6	0.50
6.3	4.7	B	TBM0J475BSEB	6	0.50
6.3	6.8	C	TBM0J685CSBA	6	0.50
6.3	6.8	C	TBM0J685CSCB	6	0.50
6.3	6.8	C	TBM0J685CSEB	6	0.50
6.3	6.8	E	TBM0J685ESCB	6	0.50
6.3	10	D	TBM0J106DSCB	8	0.63
6.3	15	E	TBM0J156ESCB	8	0.95
6.3	15	E	TBM0J156ESEB	8	0.95
6.3	22	E	TBM0J226ESEB	8	1.39
6.3	22	F	TBM0J226FSBA	8	1.39
6.3	22	F	TBM0J226FSCB	8	1.39
6.3	22	F	TBM0J226FSEA	8	1.39
6.3	22	F	TBM0J226FSEB	8	1.39
6.3	33	H	TBM0J336HSCB	8	2.08
6.3	33	H	TBM0J336HSEA	8	2.08
6.3	33	H	TBM0J336HSEB	8	2.08
6.3	47	I	TBM0J476ISCB	8	2.96
6.3	47	I	TBM0J476ISEA	8	2.96
6.3	47	I	TBM0J476ISEB	8	2.96
6.3	47	K	TBM0J476KSCB	8	2.96
6.3	68	K	TBM0J686KSCB	8	4.28
6.3	68	K	TBM0J686KSEA	8	4.28
6.3	100	L	TBM0J107LSAB	10	6.30
6.3	100	L	TBM0J107LSCB	10	6.30
6.3	100	L	TBM0J107LSEA	10	6.30
6.3	100	L	TBM0J107LSEB	10	6.30
6.3	150	M	TBM0J157MSAB	10	9.45
6.3	220	N	TBM0J227NSCB	12	13.86
6.3	330	P	TBM0J337PSAB	12	20.79
10	2.2	B	TBM1A225BSBA	6	0.50
10	2.2	B	TBM1A225BSCB	6	0.50
10	2.2	B	TBM1A225BSEA	6	0.50
10	3.3	B	TBM1A335BSBA	6	0.50
10	3.3	B	TBM1A335BSCB	6	0.50
10	3.3	B	TBM1A335BSEA	6	0.50
10	3.3	B	TBM1A335BSEB	6	0.50
10	4.7	B	TBM1A475CSEA	6	0.50
10	4.7	C	TBM1A475CSBA	6	0.50
10	4.7	C	TBM1A475CSCB	6	0.50
10	4.7	C	TBM1A475CSEB	6	0.50
10	6.8	D	TBM1A685DSCB	6	0.68
10	6.8	D	TBM1A685DSEB	6	0.68
10	10	E	TBM1A106ESBA	8	1.00
10	10	E	TBM1A106ESCB	8	1.00
10	10	E	TBM1A106ESEB	8	1.00
10	10	E	TBM1A106ESEA	8	1.00
10	15	F	TBM1A156FSCB	8	1.50
10	15	F	TBM1A156FSEB	8	1.50
10	22	H	TBM1A226HSAB	8	2.20
10	22	H	TBM1A226HSCB	8	2.20
10	22	H	TBM1A226HSEB	8	2.20
10	22	I	TBM1A226ISCB	8	2.20
10	22	I	TBM1A226ISEA	8	2.20
10	33	I	TBM1A336ISCB	8	3.30
10	33	I	TBM1A336ISEA	8	3.30
10	33	I	TBM1A336ISEB	8	3.30
10	47	J	TBM1A476JSBA	8	4.70
10	47	J	TBM1A476JSEA	8	4.70
10	47	K	TBM1A476KSAB	8	4.70
10	47	K	TBM1A476KSBA	8	4.70

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品名	tan (%)	L.C (μ A)
10	47	K	TBM1A476KSCB	8	4.70
10	47	K	TBM1A476KSEA	8	4.70
10	47	K	TBM1A476KSEB	8	4.70
10	68	L	TBM1A686LSAB	8	6.80
10	100	M	TBM1A107MSAB	10	10.00
10	100	M	TBM1A107MSEA	10	10.00
10	100	M	TBM1A107MSEB	10	10.00
10	150	N	TBM1A157NSAB	10	15.00
10	220	P	TBM1A227PSAB	12	22.00
10	220	P	TBM1A227PSCB	12	22.00
10	220	P	TBM1A227PSEB	12	22.00
16	1	A	TBM1C105ASCB	4	0.50
16	1	B	TBM1C105BSAB	4	0.50
16	1	B	TBM1C105BSBA	4	0.50
16	1	B	TBM1C105BSBB	4	0.50
16	1	B	TBM1C105BSCB	4	0.50
16	1	B	TBM1C105BSEA	4	0.50
16	1	B	TBM1C105BSEB	4	0.50
16	1	B	TBM1C105BSKB	4	0.50
16	1.5	B	TBM1C155BSCB	6	0.50
16	2.2	B	TBM1C225BSAB	6	0.50
16	2.2	B	TBM1C225BSBA	6	0.50
16	2.2	B	TBM1C225BSCB	6	0.50
16	2.2	B	TBM1C225BSEA	6	0.50
16	2.2	B	TBM1C225BSEB	6	0.50
16	2.2	B	TBM1C225BSKB	6	0.50
16	3.3	C	TBM1C335CSAB	6	0.53
16	3.3	C	TBM1C335CSBA	6	0.53
16	3.3	C	TBM1C335CSCB	6	0.53
16	3.3	C	TBM1C335CSEA	6	0.53
16	3.3	C	TBM1C335CSEB	6	0.53
16	3.3	C	TBM1C335CSKB	6	0.53
16	4.7	D	TBM1C475DSAB	6	0.75
16	4.7	D	TBM1C475DSBA	6	0.75
16	4.7	D	TBM1C475DSCB	6	0.75
16	4.7	D	TBM1C475DSEA	6	0.75
16	4.7	D	TBM1C475DSEB	6	0.75
16	4.7	D	TBM1C475DSKB	6	0.75
16	4.7	E	TBM1C475ESEA	6	0.75
16	6.8	E	TBM1C685ESAB	6	1.09
16	6.8	E	TBM1C685ESBA	6	1.09
16	6.8	E	TBM1C685ESCB	6	1.09
16	6.8	E	TBM1C685ESEA	6	1.09
16	6.8	E	TBM1C685ESEB	6	1.09
16	6.8	E	TBM1C685ESKB	6	1.09
16	10	G	TBM1C106GSAB	8	1.60
16	10	G	TBM1C106GSBA	8	1.60
16	10	G	TBM1C106GSCB	8	1.60
16	10	G	TBM1C106GSEA	8	1.60
16	10	G	TBM1C106GSEB	8	1.60
16	10	G	TBM1C106GSKB	8	1.60
16	15	I	TBM1C156ISCB	8	2.40
16	15	I	TBM1C156ISEA	8	2.40
16	15	I	TBM1C156ISEB	8	2.40
16	22	J	TBM1C226JSAB	8	3.52
16	22	J	TBM1C226JSBA	8	3.52
16	22	J	TBM1C226JSCB	8	3.52
16	22	J	TBM1C226JSEA	8	3.52
16	22	J	TBM1C226JSEB	8	3.52
16	22	J	TBM1C226JSKB	8	3.52
16	33	K	TBM1C336KSAB	8	5.28
16	33	K	TBM1C336KSBA	8	5.28
16	33	K	TBM1C336KSCB	8	5.28

データシート

■TBデップシリーズ／標準品在庫シリーズ

定格電圧 (DC.V)	静電容量 (μF)	ケース Size	品 名	tan (%)	L.C (uA)
16	33	K	TBM1C336KSEA	8	5.28
16	33	K	TBM1C336KSEB	8	5.28
16	33	K	TBM1C336KSKB	8	5.28
16	47	L	TBM1C476LSAB	8	7.52
16	47	L	TBM1C476LSBA	8	7.52
16	47	L	TBM1C476LSCB	8	7.52
16	47	L	TBM1C476LSEA	8	7.52
16	47	L	TBM1C476LSEB	8	7.52
16	47	L	TBM1C476LSKB	8	7.52
16	68	M	TBM1C686MSAB	8	10.88
16	68	M	TBM1C686MSCB	8	10.88
16	100	N	TBM1C107NSAB	10	16.00
16	100	N	TBM1C107NSCB	10	16.00
16	100	N	TBM1C107NSEA	10	16.00
16	100	N	TBM1C107NSKB	10	16.00
16	100	P	TBM1C107PSAB	10	16.00
16	150	P	TBM1C157PSAB	10	24.00
20	0.47	A	TBM1D474ASCB	4	0.50
20	1	B	TBM1D105BSBA	4	0.50
20	1	B	TBM1D105BSCB	4	0.50
20	1	B	TBM1D105BSEA	4	0.50
20	1.5	B	TBM1D155BSCB	6	0.50
20	2.2	C	TBM1D225CSCB	6	0.50
20	2.2	C	TBM1D225CSEB	6	0.50
20	4.7	E	TBM1D475ESCB	6	0.94
20	4.7	E	TBM1D475ESEB	6	0.94
20	6.8	F	TBM1D685FSCB	6	1.36
20	10	F	TBM1D106FSEA	8	2.00
20	10	H	TBM1D106HSCB	8	2.00
20	10	H	TBM1D106HSEA	8	2.00
20	10	H	TBM1D106HSEB	8	2.00
20	15	J	TBM1D156JSAB	8	3.00
20	15	J	TBM1D156JSCB	8	3.00
20	15	J	TBM1D156JSEA	8	3.00
20	22	K	TBM1D226KSAB	8	4.40
20	22	K	TBM1D226KSCB	8	4.40
20	33	L	TBM1D336LSAB	8	6.60
20	33	L	TBM1D336LSEB	8	6.60
20	47	M	TBM1D476MSAB	8	9.40
20	68	N	TBM1D686NSAB	8	13.60
20	100	P	TBM1D107PSAB	10	20.00
20	100	P	TBM1D107PSCB	10	20.00
20	100	P	TBM1D107PSEA	10	20.00
25	0.47	A	TBM1E474ASCB	4	0.50
25	1	B	TBM1E105BSAB	4	0.50
25	1	B	TBM1E105BSBA	4	0.50
25	1	B	TBM1E105BSBB	4	0.50
25	1	B	TBM1E105BSCB	4	0.50
25	1	B	TBM1E105BSEA	4	0.50
25	1	B	TBM1E105BSEB	4	0.50
25	1	B	TBM1E105BSKB	4	0.50
25	1.5	B	TBM1E155BSBA	6	0.50
25	1.5	B	TBM1E155BSCB	6	0.50
25	1.5	B	TBM1E155BSEB	6	0.50
25	2.2	C	TBM1E225CSAB	6	0.55
25	2.2	C	TBM1E225CSBA	6	0.55
25	2.2	C	TBM1E225CSBB	6	0.55
25	2.2	C	TBM1E225CSCB	6	0.55
25	2.2	C	TBM1E225CSEA	6	0.55
25	2.2	C	TBM1E225CSEB	6	0.55
25	2.2	E	TBM1E225ESEB	6	0.55
25	3.3	D	TBM1E335DSCB	6	0.83
25	3.3	D	TBM1E335DSEA	6	0.83

定格電圧 (DC.V)	静電容量 (μF)	ケース Size	品 名	tan (%)	L.C (uA)
25	3.3	D	TBM1E335DSEB	6	0.83
25	4.7	E	TBM1E475ESAB	6	1.18
25	4.7	E	TBM1E475ESBA	6	1.18
25	4.7	E	TBM1E475ESCB	6	1.18
25	4.7	E	TBM1E475ESEB	6	1.18
25	4.7	E	TBM1E475ESEA	6	1.18
25	4.7	E	TBM1E475ESEB	6	1.18
25	4.7	E	TBM1E475ESKB	6	1.18
25	6.8	G	TBM1E685GSAB	6	1.70
25	6.8	G	TBM1E685GSBA	6	1.70
25	6.8	G	TBM1E685GSCB	6	1.70
25	6.8	G	TBM1E685GSEA	6	1.70
25	6.8	G	TBM1E685GSEB	6	1.70
25	10	I	TBM1E106ISAB	8	2.50
25	10	I	TBM1E106ISBA	8	2.50
25	10	I	TBM1E106ISCB	8	2.50
25	10	I	TBM1E106ISEA	8	2.50
25	10	I	TBM1E106ISEB	8	2.50
25	10	I	TBM1E106ISKB	8	2.50
25	15	J	TBM1E156JSAB	8	3.75
25	15	J	TBM1E156JSBA	8	3.75
25	15	J	TBM1E156JSBB	8	3.75
25	15	J	TBM1E156JSCB	8	3.75
25	15	J	TBM1E156JSEA	8	3.75
25	15	J	TBM1E156JSEB	8	3.75
25	22	L	TBM1E226LSAB	8	5.50
25	22	L	TBM1E226LSBA	8	5.50
25	22	L	TBM1E226LSCB	8	5.50
25	22	L	TBM1E226LSEA	8	5.50
25	22	L	TBM1E226LSEB	8	5.50
25	22	L	TBM1E226LSKB	8	5.50
25	33	M	TBM1E336MSAB	8	8.25
25	33	M	TBM1E336MSCB	8	8.25
25	33	M	TBM1E336MSEA	8	8.25
25	33	M	TBM1E336MSEB	8	8.25
25	47	N	TBM1E476NSAB	8	11.75
25	47	N	TBM1E476NSCB	8	11.75
25	47	N	TBM1E476NSEA	8	11.75
25	47	N	TBM1E476NSEB	8	11.75
25	47	N	TBM1E476NSKB	8	11.75
25	68	N	TBM1E686NSAB	8	17.00
25	68	N	TBM1E686NSCB	8	17.00
25	68	P	TBM1E686PSAB	8	17.00
35	0.1	A	TBM1V104ASAB	4	0.50
35	0.1	A	TBM1V104ASBA	4	0.50
35	0.1	A	TBM1V104CSBB	4	0.50
35	0.1	A	TBM1V104ASCB	4	0.50
35	0.1	A	TBM1V104ASEA	4	0.50
35	0.1	A	TBM1V104ASEB	4	0.50
35	0.1	A	TBM1V104ASKB	4	0.50
35	0.1	C	TBM1V104CSCB	4	0.50
35	0.15	A	TBM1V154ASBA	4	0.50
35	0.15	A	TBM1V154ASCB	4	0.50
35	0.15	A	TBM1V154ASEA	4	0.50
35	0.15	A	TBM1V154ASEB	4	0.50
35	0.22	B	TBM1V224BSBA	4	0.50
35	0.22	B	TBM1V224BSCB	4	0.50
35	0.22	B	TBM1V224BSEA	4	0.50
35	0.22	B	TBM1V224BSEB	4	0.50
35	0.22	B	TBM1V224BSKB	4	0.50
35	0.33	B	TBM1V334BSBA	4	0.50
35	0.33	B	TBM1V334BSCB	4	0.50
35	0.33	B	TBM1V334BSEA	4	0.50
35	0.33	B	TBM1V334BSEB	4	0.50

データシート

■TBデップシリーズ／標準品在庫シリーズ

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品名	tan (%)	L.C (μ A)
35	0.33	B	TBM1V334BSKB	4	0.50
35	0.47	B	TBM1V474BSAB	4	0.50
35	0.47	B	TBM1V474BSBA	4	0.50
35	0.47	B	TBM1V474BSBB	4	0.50
35	0.47	B	TBM1V474BSCB	4	0.50
35	0.47	B	TBM1V474BSEA	4	0.50
35	0.47	B	TBM1V474BSEB	4	0.50
35	0.47	B	TBM1V474BSKB	4	0.50
35	0.68	B	TBM1V684BSCB	4	0.50
35	0.68	B	TBM1V684BSEA	4	0.50
35	0.68	B	TBM1V684BSEB	4	0.50
35	1	A	TBM1V105CSBB	4	0.50
35	1	C	TBM1V105CSAB	4	0.50
35	1	C	TBM1V105CSBA	4	0.50
35	1	C	TBM1V105CSCB	4	0.50
35	1	C	TBM1V105CSEA	4	0.50
35	1	C	TBM1V105CSEB	4	0.50
35	1	C	TBM1V105CSKB	4	0.50
35	1	D	TBM1C225CSKB	4	0.50
35	1.5	D	TBM1V155DSAB	6	0.53
35	1.5	D	TBM1V155DSBA	6	0.53
35	1.5	D	TBM1V155DSCB	6	0.53
35	1.5	D	TBM1V155DSEA	6	0.53
35	1.5	D	TBM1V155DSEB	6	0.53
35	2.2	E	TBM1V225ESAB	6	0.77
35	2.2	E	TBM1V225ESBA	6	0.77
35	2.2	E	TBM1V225ESC	6	0.77
35	2.2	E	TBM1V225ESEB	6	0.77
35	2.2	E	TBM1V225ESKB	6	0.77
35	3.3	G	TBM1V335GSAB	6	1.16
35	3.3	G	TBM1V335GSBA	6	1.16
35	3.3	G	TBM1V335GSCB	6	1.16
35	3.3	G	TBM1V335GSEA	6	1.16
35	3.3	G	TBM1V335GSEB	6	1.16
35	3.3	G	TBM1V335GSKB	6	1.16
35	4.7	H	TBM1V475HSAB	6	1.65
35	4.7	H	TBM1V475HSBA	6	1.65
35	4.7	H	TBM1V475HSCB	6	1.65
35	4.7	H	TBM1V475HSEA	6	1.65
35	4.7	H	TBM1V475HSEB	6	1.65
35	4.7	H	TBM1V475HSKB	6	1.65
35	6.8	H	TBM1V685ISEA	6	2.38
35	6.8	I	TBM1V685ISAB	6	2.38
35	6.8	I	TBM1V685ISCB	6	2.38
35	6.8	I	TBM1V685ISEB	6	2.38
35	10	J	TBM1V106JSAB	8	3.50
35	10	J	TBM1V106JSBA	8	3.50
35	10	J	TBM1V106JSCB	8	3.50
35	10	J	TBM1V106JSEA	8	3.50
35	10	J	TBM1V106JSEB	8	3.50
35	10	J	TBM1V106JSKB	8	3.50
35	15	L	TBM1V156LSAB	8	5.25
35	15	L	TBM1V156LSCB	8	5.25
35	15	L	TBM1V156LSEA	8	5.25
35	15	L	TBM1V156LSEB	8	5.25
35	22	M	TBM1V226MSAB	8	7.70
35	22	M	TBM1V226MSCB	8	7.70
35	22	M	TBM1V226MSEA	8	7.70
35	22	M	TBM1V226MSEB	8	7.70
35	22	M	TBM1V226MSKB	8	7.70
35	33	N	TBM1V336NSAB	8	11.55
35	33	N	TBM1V336NSCB	8	11.55

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品名	tan (%)	L.C (μ A)
35	47	N	TBM1V476NSAB	8	16.45
35	47	N	TBM1V476NSEA	8	16.45
35	47	N	TBM1V476NSKB	8	16.45
35	47	P	TBM1V476PSAB	8	16.45
50	0.1	B	TBM1H104BSCB	4	0.50
50	0.1	B	TBM1H104BSEB	4	0.50
50	0.1	B	TBM1H104BSKB	4	0.50
50	0.15	B	TBM1H154BSCB	4	0.50
50	0.22	B	TBM1H224BSCB	4	0.50
50	0.22	B	TBM1H224BSEA	4	0.50
50	0.22	B	TBM1H224BSKB	4	0.50
50	0.33	B	TBM1H334BSCB	4	0.50
50	0.33	C	TBM1H334CSCB	4	0.50
50	0.33	C	TBM1H334CSEB	4	0.50
50	0.47	B	TBM1H474BSCB	4	0.50
50	0.47	D	TBM1H474DSCB	4	0.50
50	0.47	D	TBM1H474DSEA	4	0.50
50	0.47	D	TBM1H474DSEB	4	0.50
50	0.68	E	TBM1H684ESC	4	0.50
50	1	F	TBM1H105FSBA	4	0.50
50	1	F	TBM1H105FSCB	4	0.50
50	1	F	TBM1H105FSEA	4	0.50
50	1	F	TBM1H105FSEB	4	0.50
50	2.2	J	TBM1H225JSAB	6	1.10
50	2.2	J	TBM1H225JSCB	6	1.10
50	2.2	J	TBM1H225JSEA	6	1.10
50	3.3	K	TBM1H335KSCB	6	1.65
50	3.3	L	TBM1H335LSAB	6	1.65
50	3.3	L	TBM1H335LSEB	6	1.65
50	4.7	L	TBM1H475LSAB	6	2.35
50	4.7	L	TBM1H475LSCB	6	2.35
50	4.7	L	TBM1H475LSEB	6	2.35
50	6.8	M	TBM1H685MSAB	6	3.40
50	10	N	TBM1H106NSAB	8	5.00
50	10	P	TBM1H106PSAB	8	5.00
50	100	N	TBM1H107NSAB	10	50.00

データシート


■TDデブシリーズ/小型品(受注生産品)

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品 名	tan (%)	L.C (μ A)
6.3	6.8	D	TDMOJ685DSCB	6	0.50
6.3	10	E	TDMOJ106ESCB	8	0.63
6.3	10	F	TDMOJ106FSCB	8	0.63
6.3	10	F	TDMOJ156FSCB	8	0.63
6.3	22	G	TDMOJ226GSCB	8	1.39
6.3	33	H	TDMOJ336HSCB	8	2.08
6.3	68	J	TDMOJ686JSCB	8	4.28
10	2.2	B	TDM1A225BSCB	6	0.50
10	2.2	C	TDM1A225CSCB	6	0.50
10	4.7	D	TDM1A475DSBA	6	0.50
10	4.7	D	TDM1A475DSCB	6	0.50
10	4.7	D	TDM1A475DSEA	6	0.50
10	4.7	D	TDM1A475DSEB	6	0.50
10	4.7	J	TDM1A476JSBA	6	0.50
10	33	I	TDM1A336ISCB	8	3.30
10	33	I	TDM1A336ISKB	8	3.30
10	47	J	TDM1A476JSCB	8	4.70
16	2.2	C	TDM1C225CSBA	6	0.50
16	2.2	C	TDM1C225CSCB	6	0.50
16	2.2	C	TDM1C225CSEB	6	0.50
16	2.2	C	TDM1C225CSKB	6	0.50
16	3.3	D	TDM1C335DSCB	6	0.53
16	3.3	D	TDM1C335DSEB	6	0.53
16	3.3	D	TDM1C335DSKB	6	0.53
16	4.7	E	TDM1C475ESCB	6	0.75
16	4.7	E	TDM1C475ESEB	6	0.75
16	4.7	E	TDM1C475ESKB	6	0.75
16	6.8	F	TDM1C685FSCB	6	1.09
16	10	G	TDM1C106GSBA	8	1.60
16	10	G	TDM1C106GSCB	8	1.60
16	10	G	TDM1C106GSEA	8	1.60
16	10	G	TDM1C106GSEB	8	1.60
16	10	G	TDM1C106GSKB	8	1.60
16	22	I	TDM1C226ISBA	8	3.52
16	22	I	TDM1C226ISCB	8	3.52
16	22	I	TDM1C226ISKB	8	3.52
16	22	J	TDM1C226JSKB	8	3.52
16	33	J	TDM1C336JSAB	8	5.28
16	33	J	TDM1C336JSCB	8	5.28
16	33	J	TDM1C336JSEB	8	5.28
16	33	J	TDM1C336JSKB	8	5.28
20	2.2	E	TDM1D225ESCB	6	0.50
20	10	G	TDM1D106GSCB	8	2.00
20	10	H	TDM1D106HSCB	8	2.00
25	0.33	A	TDM1E334ASCB	4	0.50
25	0.33	A	TDM1E334ASER	4	0.50
25	1	C	TDM1E105CSCB	4	0.50
25	1	C	TDM1E105CSKB	4	0.50
25	2.2	E	TDM1E225ESCB	6	0.55
25	4.7	G	TDM1E475GSCB	6	1.18
25	4.7	G	TDM1E475GSKB	6	1.18
25	10	I	TDM1E106ISBA	8	2.50
25	10	I	TDM1E106ISCB	8	2.50
25	10	I	TDM1E106ISEB	8	2.50
25	10	I	TDM1E106ISKB	8	2.50
35	0.1	A	TDM1V104ASAB	4	0.50
35	0.1	A	TDM1V104ASCB	4	0.50
35	0.15	A	TDM1V154ASBA	4	0.50
35	0.15	A	TDM1V154ASCB	4	0.50
35	0.22	A	TDM1V224ASCB	4	0.50
35	0.33	B	TDM1V334BSCB	4	0.50
35	0.47	B	TDM1V474BSCB	4	0.50
35	0.47	B	TDM1V474BSEB	4	0.50

定格電圧 (DC.V)	静電容量 (μ F)	ケース Size	品 名	tan (%)	L.C (μ A)
35	0.68	C	TDM1V684CSCB	4	0.50
35	1	C	TDM1V105CSKB	4	0.50
35	1	D	TDM1V105DSCB	4	0.50
35	1	D	TDM1V105DSEB	4	0.50
35	1	D	TDM1V105DSKB	4	0.50
35	2.2	F	TDM1V225FSCB	6	0.77
35	2.2	F	TDM1V225FSEA	6	0.77
35	2.2	F	TDM1V225FSEB	6	0.77
35	2.2	F	TDM1V225FSKB	6	0.77
35	3.3	G	TDM1V335GSCB	6	1.16
35	4.7	H	TDM1V475HSCB	6	1.65
35	6.8	I	TDM1V685ISCB	6	2.38
35	6.8	I	TDM1V685ISKB	6	2.38
35	10	J	TDM1V106JSEB	8	3.50
35	47	P	TDM1V476PSAB	8	16.45

ディップシリーズ外形寸法表


■外形寸法表



TB シリーズ	D/H	A	B	C	D	E	F	G	H
	D/max	4.5	4.5	5.0	5.0	5.0	5.5	5.5	6.0
	H/max	7.5	8.0	8.0	9.0	9.5	10.0	10.5	10.5
	D/H <th>I</th> <th>J</th> <th>K</th> <th>L</th> <th>M</th> <th>N</th> <th>P</th> <th></th>	I	J	K	L	M	N	P	
D/max	6.0	6.5	7.0	7.5	8.5	9.0	9.5		
H/max	11.0	11.0	12.5	13.5	14.5	15.5	16.0	(mm)	

TD シリーズ	D/H	A	B	C	D	E	F	G	H
	D/max	3.4	3.7	3.9	4.0	4.0	4.5	5.0	5.2
	H/max	5.4	6.0	6.5	7.0	7.5	8.0	8.0	8.0
	D/H <th>I</th> <th>J</th> <th>K</th> <th>L</th> <th>M</th> <th>N</th> <th>P</th> <th></th>	I	J	K	L	M	N	P	
D/max	5.5	6.0	-	-	-	-	-	-	
H/max	10.0	10.0	-	-	-	-	-	(mm)	

■アモパッケテーピング寸法表



Item	Symbol	Length (B/AE)	Tolerance (B/AE)
lead diameter	d	0.5	±0.05
pitch per parts	p	12.7	±1.0
pitch per hole	p ₀	12.7	±0.2
interval (hole to lead)	p ₁ /P ₁	3.85/5.1	±0.7
interval (hole to part)	P ₂	6.35	±0.5
interval (lead to lead)	F ₁ /F ₂	2.2/5.0	±0.5
parts alignment (F-R)	▲H	0	±2.0
tape width	W	18.0	±0.5
hole to down tape width	W ₀	6.0	±0.5
hole position	W ₁	9.0	+0.75, -0.5
hole to down tape position	W ₂	2.0	max.
part to tape center	H	19.0	±0.5
lead forming H	H ₀	16.0	±0.5
part H	H ₁	32.25	max.
feed hole diameter	D ₀	4.0	±0.3
lead exposure	L ₁	7.0	+2.0, -2.5

■アモパック (つづら折りテーピング) 梱包数量表

ケースサイズ	Inner Box	Outer Box
A~C	3,500 pcs	6 I.B.(21KP)
D~G	3,000 pcs	6 I.B.(18KP)
H~J	2,500 pcs	6 I.B.(15KP)
K~L	2,000 pcs	6 I.B.(12KP)

■バルク梱包数量表

ケースサイズ	Vinyl Bag	Inner Box	Outer Box
A~B	500 pcs	16 V.B.(8KP)	9 I.B.(72KP)
C~H	500 pcs	14 V.B.(7KP)	9 I.B.(63KP)
I~K	300 pcs	14 V.B.(4.2KP)	9 I.B.(37.5KP)
L~P	200 pcs	10 V.B.(2KP)	9 I.B.(18KP)

※日本向け100/200gバッグあります。

■ディップ形品名呼称方法

