

Subminiature Rotary Coded Switches waterproof




Specifications:


Contact rating:	switching: 150 mA, 42 V non-switching: 200 mA, 42 V
Contact resistance:	< 80 mΩ
Insulation resistance:	> 100 MΩ
Dielectric strength:	250 V, 50 Hz for the duration of 1 minute
Operating temperature:	-40 °C to +85 °C
Storage temperature:	-40 °C to +85 °C
Mechanical life:	minimum 10 000 operations
Terminals:	phosphor bronze, gold-plated over nickel barrier
Material:	case: PA6T meets UL 94 V-0, cover light grey, base black rotor: grey, inverse type beige
Protection:	IP 67
Mounting:	on pc-board with spacing 2.54 mm
Soldering conditions:	wave-soldering – max. 10 sec, 260 °C pre-heat – max. 70 sec, max. 120 °C

Models: Code


DRS 60010	BCD
DRS 60110	BCD Inverse
DRS 60016	Hexadecimal
DRS 60116	Hexadecimal Inverse




DRS 61010	BCD
DRS 61110	BCD Inverse
DRS 61016	Hexadecimal
DRS 61116	Hexadecimal Inverse



DRR 60010	BCD
DRR 60110	BCD Inverse
DRR 60016	Hexadecimal
DRR 60116	Hexadecimal Inverse



Special version:



Spacing 2.54 mm

Additional to type number: -1

Example for order: DRR 60010-1

