

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Socket, straight, M8, coding: A, PCB mounting, SMD reflow, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238989

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1412254
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQ
Product key	ABQHCT
GTIN	4046356988964
Weight per piece (including packing)	5.11 g
Weight per piece (excluding packing)	5.11 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Number of positions	8
Seal present	yes
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\leq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC 30 V DC
Nominal current I_N	1.5 A

Connection data

Connection method	SMD reflow
-------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

1412254

<https://www.phoenixcontact.com/in/products/1412254>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
	-40 °C ... 105 °C (without mechanical actuation)

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications


Type of packaging	Belt
-------------------	------

1412254

<https://www.phoenixcontact.com/in/products/1412254>

Drawings

Schematic diagram



Connector pin assignment of M8 socket, 8-pos., view of socket side

SACC-CIP-M8FS-8P SMD R32 - Contact carrier



1412254

<https://www.phoenixcontact.com/in/products/1412254>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1412254>

	cULus Recognized			
	Approval ID: E221474-20160506			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	1.5 A	-	-

SACC-CIP-M8FS-8P SMD R32 - Contact carrier



1412254

<https://www.phoenixcontact.com/in/products/1412254>

Classifications

ECLASS

ECLASS-13.0	27440223
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	74b96dbb-5cf5-4a53-98fc-1a6c9b20df4d

SACC-CIP-M8FS-8P SMD R32 - Contact carrier



1412254

<https://www.phoenixcontact.com/in/products/1412254>

Accessories

SACC-CIP-M8FS-8P SMD-SP - Sample set

1418664

<https://www.phoenixcontact.com/in/products/1418664>



Sample set, 8-position, Socket, straight, M8, coding: A, PCB mounting, SMD, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239219

SACC-BP-F-M8/M12 SMD - Housing screw connection

1412506

<https://www.phoenixcontact.com/in/products/1412506>



Housing screw connection, Socket, M8, Rear mounting, M12 x 1, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239003

SACC-CIP-M8FS-8P SMD R32 - Contact carrier

1412254

<https://www.phoenixcontact.com/in/products/1412254>



SACC-FP-F-M8/M10 SMD - Housing screw connection

1412504

<https://www.phoenixcontact.com/in/products/1412504>

M8 female connector, front mounting SMD with M10 screw fastening



SACC-FP-F-M8/PRESS SMD - Housing screw connection

1412501

<https://www.phoenixcontact.com/in/products/1412501>

M8 socket, press-in mounting



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in