




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin (Sn)**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **250 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Orientation	Straight
Mating Pin Diameter	2.1 mm[.082 in]
Wire Contact Termination Area Plating Material Finish	Bright
Wire Contact Termination Area Plating Thickness	.4 µm[15.74 µin]
Contact Type	Socket
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	10 A



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	3.3 mm[.13 in]
Wire Size	.52 – 2.27 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-480349-6 01P CMNL PLUG HSG F/H BLU	 TE Part # 1-480720-0 02P CMNL PLUG HSG W/LOK NATL	 TE Part # 171382-1 MNL PANEL MOUNT PLUG 6P	 TE Part # 171267-1 CIRCUIT HSG PLUG
 TE Part # 3-480425-0 04P CMNL PLG HSG, H-TEMP	 TE Part # 1-480288-0 12P CMNL CAP HSG M/M NATL	 TE Part # 1-480305-9 03P CMNL CAP HSG F/H BLK	 TE Part # 1-480438-0 16P CMNL PLUG HSG M/M NATL
 TE Part # 1-480318-4 02P CMNL PLUG HSG F/H YELL	 TE Part # 1-480319-4 02P CMNL CAP HSG F/H YELL	 TE Part # 1-480319-9 02P CMNL CAP HSG F/H BLK	 TE Part # 1-480351-2 01P CMNL CAP HSG RED
 TE Part # 1-480388-0 03P CMNL PLUG HSG F/H BLK	 TE Part # 1-480393-1 02P CMNL PLUG HSG F/H BLK	 TE Part # 1-480425-0 04P CMNL PLUG HSG P/M NATL	 TE Part # 1-480271-0 06P CMNL CAP HSG M/M NATL




TE Part # 1-480276-0
06P CMNL CAP HSG P/M NATL



TE Part # 1-480498-1
02P CMNL CAP HSG F/H BLK



TE Part # 1-480283-0
08P CMNL PLUG HSG M/M NATL




TE Part # 1-480721-0
03P CMNL PLUG HSG W/LOK NATL

Also in the Series | Commercial MATE-N-LOK



Connector Contacts(150)



Crimp Wire Pins, Tabs & Ferrules(2)



Power Contacts(146)



Rectangular Connector Housings(118)



Rectangular Power Connectors(182)



Standard Circular Connectors(2)



Standard Rectangular Connectors(126)

Customers Also Bought



TE Part #316040-3
DYNAMIC D-5 REC CONT. S L/P




TE Part #CAT-D9934-A75E
Header Assembly: Wire-to-Board, 15A, gold or tin plated



TE Part #CAT-D9934-A75F
DYNAMIC 3200 HDR ASSY



TE Part #CAT-D9934-A75B
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V



TE Part #1-292161-2
CT P/HDR ASSY V 12P W/KINK NAT



TE Part #171827-1
MIC CAP 17P



Documents

Product Drawings

M-N-L SKT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170121-4_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170121-4_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170121-4_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English