



Dataman 48Pro4C

The Dataman 48Pro4C is a super fast PC based universal 48-pin programmer with ISP capabilities and USB 2.0 connectivity. The 48Pro4C is built to meet the demands of development labs and field engineers for cost effective universal programming.

Supporting over 138,000 (May 2026) devices with new support being added monthly, the Dataman 48Pro4C gives you the freedom to choose the optimal device for your requirements. Using the built-in, in-system programming (ISP) connector, the programmer is able to program ISP compatible chips in circuit.



Hardware

General

- The 48Pro4C programmer offers the same advanced features as the 48Pro2C programmer but with improved hardware: Better pindriver for low-voltage devices, higher programming speeds and a more powerful programming core (FPGA).
- FPGA based totally reconfigurable 48 powerful TTL pindrivers provide H, L, pull-up, pull-down and read capability for each pin of the socket. Advanced pindrivers incorporate high-quality high-speed circuitry to deliver signals without overshoot or ground bounce for all supported devices. Improved pindrivers operate down to 1.8V and provide the capability for independent analog voltage measurement on each pin.
- The programmer performs device insertion and contact tests before programming each device. These capabilities, supported by overcurrent protection and signature-byte check, help prevent chip damage due to operator error.
- Selftest capability allows diagnostics in the software to thoroughly check the health of the programmer.
- Built-in protection circuits eliminate damage to the programmer and/or programmed devices due to environment or operator failure. All the inputs of the 48Pro4C programmer, including ZIF socket, connection to PC and power supply input are protected against ESD up to 15kV.
- The 48Pro4C programmer performs programming verification at the marginal levels of supply voltage, improving programming yield and guaranteeing long data retention.
- Wide range of adapters are available to handle devices in PLCC, JLCC, SOIC, SDIP, SOP, PSOP, SSOP, TSOP, TSOPII, TSSOP, QFP, PQFP, TQFP, VQFP, QFN (MLF), SON, BGA, EBGA, FBGA, VFBGA, UBGA, FTBGA, LAP, CSP, SCSP, LQFP, MQFP, HVQFN, QLP, QIP and other packages.

Programmer Specification

- 1 x universal programming module (1 x 48-pin DIL ZIF socket and 1 x 20-pin ISP connector)
- Power and operation status LEDs
- USB 2.0 high-speed compatible port
- Protection against surge and ESD on power supply input
- Banana jack for ESD wrist strap connection
- Banana jack for connection to ground

Features...

- Programming speeds of more than 6 MB/s for capable devices
- Programs 2 GB eMMC NAND Flash in less than 365 seconds
- Over 138,000 (May 2026) devices supported with new devices added monthly
- 48 powerful universal pin drivers for programming a wide range of devices
- Low-voltage support operating down to 1.8V
- ISP support
- Hi-speed USB 2.0 connectivity
- ESD protection on all inputs
- Easy to use control software compatible with Windows® 10 and Windows® 11
- Comprehensive 3 year parts and labour warranty



Free Life-Time
Technical Support



Free Life-Time
Software Updates

Module Specification

Base Unit (DAC)

- On-board intelligence: powerful microprocessor and FPGA based state machine
- Three D/A converters for VCCP, VPP1, VPP2 with controllable rise and fall time
- VCCP range 0..7V/1A
- VPP1, VPP2 range 0..26V/1A
- Selftest capability

ZIF Socket

- 48-pin DIL ZIF socket accepts both 300/600 mil devices up to 48-pin
- 48 x universal pindrivers
- VCCP, VPP1, VPP2 can be connected to each pin
- Perfect ground for each pin
- Each pin supports independent analog voltage measurement
- FPGA based TTL driver provides H, L, CLK, pull-up, pull-down on all pindriver pins
- Analog pindriver output level selectable from 1.2V up to 26V
- Current limitation, overcurrent shutdown, power failure shutdown
- ESD protection on each pin (IEC1000-4-2: 15kV air, 8kV contact)
- Each pin is continuity tested before every programming operation

ISP Connector

- 20-pin male type with misinsertion lock
- 6 x TTL pindrivers provide H, L, CLK, pull-up, pull-down; level H selectable from 1.8V up to 5V to handle all (including low-voltage) devices
- Each TTL pindriver pin supports independent analog voltage measurement
- 1 x VCCP voltage (range 2V..7V/100mA) can be applied to two pins
- Programmed chip voltage (VCCP) with both source/sink capability and voltage sense
- 1 x VPP voltage (range 2V..25V/50mA) can be applied to six pins
- Target system supply voltage (range 2V..6V/250mA)
- ESD protection on each pin (IEC1000-4-2: 15kV air, 8kV contact)
- Two output signals, which indicate state of work result = LED OK and LED Error (active level: min 1.8V)
- Input signal, switch YES! equivalent (active level: max. 0.8V)

Software

User Interface

- The programmer is driven by an easy-to-use control program with pull-down menus, hot keys and on-line help. Selecting a device is performed by its class, by manufacturer or simply by typing a fragment of the vendor name and/or part number.
- Standard device-related commands (read, blank check, program, verify, erase) are enhanced by test functions (insertion test, signature-byte check) and additional special functions (autoincrement serialisation, production mode - programming starts immediately after chip is inserted).
- All known data formats are supported. Automatic file format detection and conversion performed during loading of file.
- The versatile auto-increment function allows each programmed device to be assigned an individual or incrementing serial number. This function also enables the operator to use serial numbers or device identification signatures from an external file.
- The software provides extensive information about programmable devices including detailed drawings of all available packages. The software also provides explanations of chip labelling (prefixes and suffixes).

- The software provides full information for ISP implementation: Description of ISP connector pins, recommended target design and other necessary details.
- The remote control feature allows the software to be flow controlled by another application - either using .BAT file commands or DLL file (C/PAS/VBASIC/.NET).
- Multiple devices can be programmed and tested via a JTAG chain: JTAG chain (ISP-Jam), JTAG chain (ISP-VME), JTAG chain (ISP-SVF) or JTAG chain (ISP-STP).
- Multiple 48Pro4C programmers can be operated from the same PC creating a high-volume production environment with all the benefits of the standard 48Pro4C. Up to eight 48Pro4C programmers can be connected simultaneously providing a highly scalable gang programming system.

Device Support

The Dataman 48Pro4C supports over 138,000 (May 2026) of the most popular devices in use today - with new devices being added monthly. Dataman 48Pro4C coverage includes the following device types:

Programmer (ZIF Socket)

Parallel NAND Flash, Serial NAND Flash, eMMC, eMCP, eSD, Multi-Chip, Serial NOR Flash, Parallel NOR Flash, EPROM, EEPROM, mDOC H3, FRAM, MRAM, NV RAM, Serial EEPROM, Serial FRAM, Serial MRAM, Serial NV RAM, Serial ReRAM, Configuration (EE)PROM, 1-Wire E(E)PROM, PLD, SPLD/CPLD, FPGA, Clocks, SoC and Espressif modules, Microcontrollers

Programmer (ISP Connector)

Serial EEPROM, 1-Wire EEPROM, Serial NOR Flash, Configuration (EE)PROM, Serial FRAM, Microcontrollers, PLD, FPGA

Package Includes

- **Dataman 48Pro4C Super Fast Universal ISP Programmer**
Dimensions: 146 x 100 x 64mm (5.7 x 3.9 x 2.5inches)
Weight: 0.6Kg (1.32lbs)
- Switching Power Adapter
Operating voltage: 100-240V AC
Power consumption: max. 24W active / approx. 3W sleep
- Moulded USB cable
- ISP cable
- Diagnostic POD for selftest of the programmer
- Diagnostic POD for selftest of the ISP connector
- Anti-dust cover for ZIF socket
- Quick start guide
- Optional range of adapters and socket converters also available

Warranty and Support

- 30 day money back guarantee* - If you don't like it, send it back
- 3 year guarantee - 3 year parts and labour warranty, on the 48Pro4C universal programmer
- Life-time technical support - 48Pro4C technical support is available free via our website and telephone helpdesk for life
- Life-time software updates - 48Pro4C software updates are available free via our website for life

*Applies to orders from Dataman UK/US offices only



www.dataman.com

In the UK...

Dataman Programmers Ltd.
Unit 2 Newton Hall, Dorchester
Road, Maiden Newton, Dorset
DT2 0BD, UK
Tel (01300) 320719
Fax (01300) 321012

In the US...

Dataman Inc.
215 East Michigan Avenue
Orange City, Florida 32763
USA
Tel (386) 774-7785
Fax (386) 774-7796

Available from...