

Product datasheet

Specifications



Motor Management, TeSys T, motor controller, bypass, 24 VDC

Local distributor code:

398123327

LTM9BPS

EAN Code: 3606480420481

Main

Range	TeSys
product name	TeSys T
Supply	Via connector
Supply voltage limits	12...48 V DC
Communication port protocol	10/100BASE-T
Current consumption	32...44 mA

Complementary

Width	26 mm
Height	110 mm
Depth	70 mm
Net weight	0.2 kg

Environment

Ambient air temperature for operation	-10...60 °C
Ambient air temperature for storage	-25...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Logistical informations

Country of origin	CN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------


Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.



[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	Fc01c523-9a07-4dfa-988f-c721d4816782
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins