

FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch



1539667

<https://www.phoenixcontact.com/gb/products/1539667>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Security-enabled Ethernet gigabit modular switch with slots for twenty-four 10/100/1000 Mbps copper or 100/1000 Mbps SFP ports and four 1000/10 000 Mbps SFP ports using hot-swappable rear modules



Product description

Developed according to IEC 61850-3 (Ambient conditions)

Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- Layer 2 and Layer 3 functions
- Modules allow device connections to expand from 10/100 Mbps to 1000 Mbps, and uplink connections from 1 Gbps to 10 Gbps
- Extensive security functions for remote access, local access and network access areas
- 28-port rack-mount switch with required modular port and power supplies
- Hot-swappable port and power supply modules
- NAT, Stateful Firewall and IPSec VPN
- IEEE 1588 v2 precision timing support

Commercial data

Item number	1539667
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNN511
Product key	DNN511
GTIN	4067923012554
Weight per piece (including packing)	7,859 g
Weight per piece (excluding packing)	5,729 g
Customs tariff number	85176200
Country of origin	CA

FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch



1539667

<https://www.phoenixcontact.com/gb/products/1539667>

Technical data

Dimensions

Width	486.2 mm
Height	44.4 mm
Depth	446.7 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Mounting

Mounting type	Rack mount, includes brackets
---------------	-------------------------------

Interfaces

Ethernet

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
No. of channels	RJ45 or SFP

Ethernet (SFP)

Connection method	SFP
Transmission speed	1000/10,000 Mbps (full duplex)
Transmission physics	Depending on the SFP module

Output data

Digital:

Output name	Alarm relay output: 24 V DC, 1 A maximum
-------------	--

Product properties

Product type	Switch
Product family	Managed Switch EP7000

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Switch functions

Signal contact control voltage	24 V DC
Signal contact control current	1 A
MAC address table	16k

FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch



1539667

<https://www.phoenixcontact.com/gb/products/1539667>

Electrical properties

Maximum power dissipation for nominal condition	60 W
Supply	
Supply voltage	Based on modular power supplies used
Function	
Signal contact control voltage	24 V DC
Signal contact control current	1 A

Connection data

Connection technology	
Connection name	Power supply
Power supply	
Connection method	Screw connection
Conductor cross section, rigid	0.2 mm² ... 2.5 mm²
Conductor cross section, flexible	0.2 mm² ... 2.5 mm²
Conductor cross section AWG	24 ... 12

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (Type tested to 85 °C for 16 hours)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

Approvals

Conformity/Approvals	
Conformance	CE-compliant

EMC data

Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005
----------------	--


FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch

1539667


<https://www.phoenixcontact.com/gb/products/1539667>

Drawings

Connection diagram



Connection diagram



FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch



1539667
<https://www.phoenixcontact.com/gb/products/1539667>

Classifications

ECLASS

ECLASS-13.0	19170401
-------------	----------

ETIM

ETIM 9.0	EC000734
----------	----------

FL SWITCH EP7528R-L3F1 - Industrial Ethernet Switch



1539667

<https://www.phoenixcontact.com/gb/products/1539667>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	N,N-dimethylacetamide(CAS: 127-19-5)
	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead titanium trioxide(CAS: 12060-00-3)
	Orange lead (lead tetroxide)(CAS: 1314-41-6)
	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Terphenyl, hydrogenated(CAS: 61788-32-7)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk