

DSE201 C50 AC30 - N Blue



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs
Residual Current Circuit Breakers with Overcurrent Protection RCBO

General Information

Extended Product Type:	DSE201 C50 AC30 - N Blue
Product ID:	2CSR255051R1504
EAN:	8012542349433
Catalog Description:	DSE201 C50 AC30 - N Blue
Long Description:	DSE201 is a 1P+N residual current circuit breaker with overcurrent protection (RCBO) in one module for the protection against short-circuit currents, overload, earth fault currents, in direct contacts, additional protection against direct contacts (30 mA versions). DSE201 is equipped with supply neutral wire and functional earth wire.

Additional Information

Country of Origin:	Italy (IT)
Customs Tariff Number:	85363030
Data Sheet, Technical Information:	9AKK106930A0940
Declaration of Conformity - CE:	9AKK106713A5595
EAN:	8012542349433
ETIM 4:	EC000905 - Earth leakage circuit breaker
ETIM 5:	EC000905 - Earth leakage circuit breaker
ETIM 6:	EC000905 - Earth leakage circuit breaker
Instructions and Manuals:	9AKK106930A0912
Invoice Description:	DSE201 C50 AC30 - N Blue
Minimum Order Quantity:	1 piece
Number of Poles:	2
Number of Protected Poles:	1
Object Classification Code:	Q
Operating Characteristic:	Instantaneous
Options Provided:	-
Package Level 1 EAN:	8012542349433
Package Level 1 Gross Weight:	0.220 kg
Package Level 1 Height:	0.088 m
Package Level 1 Length:	0.143 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.036 m
Position of Neutral Terminals:	Right
Power Loss:	5.3 W
Product Main Type:	DSE201
Product Name:	Residual Current Circuit Breaker with Overcurrent Protection
Product Net Depth:	0.069 m
Product Net Height:	0.115 m
Product Net Weight:	0.200 kg
Product Net Width:	0.018 m
Rated Current (I_n):	50 A
Rated Operational Voltage:	230-240 V AC
Rated Residual Current:	30 mA
Rated Short-Circuit Capacity (I_{cn}):	6 kA
RoHS Date:	20140630
RoHS Information:	2CSC422006K2701
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Standards:	IEC 61009-1 IEC 61009-2-2 AS/NZS 61009-1
Tripping Characteristic:	C
Type of Residual Current:	AC type
Accessories Available:	No

