

22759/41-12-0

✓ ACTIVE

RAYCHEM


TE Internal #: EG4118-000

600 V, Nickel-Coated Copper, 12 AWG, -65 – 200 °C, Hook Up Wire

[View on TE.com >](#)



Wire & Cable > Hook Up Wire > SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire



Cable Type: **MIL-DTL-22759**
Operating Voltage: **600 V**
Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**
Conductor Material: **Nickel-Coated Copper**
Wire Size: **12 AWG**

[All SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire \(235\)](#)

Features

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Cable Color	Black
Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Nickel-Coated Copper
Wire Color (Base)	Black

Dimensions

Wire Size	12 AWG
-----------	--------

Usage Conditions

Cable Type	MIL-DTL-22759
Operating Temperature Range	-65 – 200 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # C60253-000
D-200-84

Customers Also Bought

TE Part #DT04-4P-E008
REC, 4P, GRY, N, XCAP

TE Part #W4P
WEDGE LOCK, 4P, REC, GRN, DT

TE Part #C5001PC26A1
THERMISTOR ASSEMBLY

Documents

22759/41-12-0

English

22759/41-12-0

600 V, Nickel-Coated Copper, 12 AWG, -65 – 200 °C, Hook Up Wire



[Datasheets & Catalog Pages](#)

[Raychem Wire and Cable Quick Reference Guide](#)

English