


Rotterdam

OEKO-TEX®
 CONFIDENCE IN TEXTILES
STANDARD 100
 1012048 Centexbel
Tested for harmful substances.
www.oeko-tex.com/standard100




Rain trousers

Light, supple, durable, maintenance-friendly, comfortable and a rock-solid protection: these Rotterdam rain trousers are the best of their kind on the market. These simple rain trousers with elastic waist and narrowing at the leg ends by press studs are an impenetrable barrier against water and wind thanks to the Flexothane® fabric. Defy the natural elements with Flexothane® rain gear!



Rain trousers

Rotterdam - 4500A2FC1

European Standards: (based upon size L)

- » EN 343 : 2019 / Class 4-1-X
- » EN ISO 13688 : 2013

Exterior:

- » Leg narrowing by press studs
- » Elasticated waist

Fabric:

Flexothane® Classic: 100% polyamide knitting with PU coating; ± 180 g/m²

Sizes:

XS - XXXXL

Colour:

- » A41 Green Khaki
- » B90 Navy blue
- » C38 Orange
- » H45 Royal Blue
- » Y58 Yellow

Combining products:

3792 – 4820 – 4899

Packaging:

20 pieces per box

Wash and care instructions:



SIOEN head office

Fabriekstraat 23

B-8850 Ardoorie

Belgium

T: +32 (51) 740 800

F: +32 (51) 740 962

www.sioen-ppc.com



**Discover
our products**

© 2020 Sioen Apparel - Protection through Innovation, Flexothane®, Siopor® and the SIOEN logo are trademarks of the Sioen Industries Group.

Please note that all information given in this document is intended to be useful and informative and is correct to the best of our knowledge at time of print. No liability can be accepted for inaccuracies or omissions. The right is reserved to amend this information without prior notice. All our technical files, style descriptions, presentations, designs and drawings, give the latest update of the standards and design or style features of each product. However, delivered products may comply with previous standards, design or style features. For that Sioen disclaims any liability whatsoever. Contact our sales for full information if specific requirements are needed.