

Specifications



Eaton 216543

Eaton Moeller® series M22 Flush mounting plate, 2 mounting locations

General specifications

PRODUCT NAME	Eaton Moeller® series M22 Accessory Flush mounting plate
CATALOG NUMBER	216543
MODEL CODE	M22-E2
EAN	4015082165437
PRODUCT LENGTH/DEPTH	3 mm
PRODUCT HEIGHT	72 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	0.076 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	EN 60947-5 IEC 60947-5 CSA Std. C22.2 No. 14-05 CSA Std. C22.2 No. 94-91 UL 508 VDE CSA CSA File No.: 012528 CSA-C22.2 No. 14-05 UL File No.: E29184 CE CSA Class No.: 3211-03 UL Category Control No.: NKCR CSA-C22.2 No. 94-91 IEC/EN 60947-5 UL

Features & Functions

COLOR	Gray
MATERIAL	Aluminum
NUMBER OF LOCATIONS	2
RAL-NUMBER	7035

Climatic environmental conditions

AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE - MAX	70 °C

Contacts

FORCE FOR POSITIVE OPENING - MIN	0 N
---	-----

General

DEGREE OF PROTECTION	IP65 Only in conjunction with a suitable enclosure and correct mounting NEMA 4X, 13
OPENING DIAMETER	22 mm
TYPE	Surface mounting enclosure

Communication

CONNECTION TO SMARTWIRE-DT	No
-----------------------------------	----

Design verification

EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is

observed.

Resources

CATALOGUES

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

[Flip catalog - Product Range Catalog - Command and indication](#)

DECLARATIONS OF CONFORMITY

[DA-DC-00004135.pdf](#)

[DA-DC-00004157.pdf](#)

DRAWINGS

[eaton-operating-mounting-m22-accessory-dimensions-003.eps](#)

[eaton-operating-mounting-m22-accessory-3d-drawing-002.eps](#)

[eaton-operating-button-symbol-007.eps](#)

ECAD MODEL

[ETN.216543.edz](#)

FLYERS

[eaton-rmq-titan-selection-aid-brochure-fl047002-en-us.pdf](#)

INSTALLATION INSTRUCTIONS

[IL04716003Z](#)

INSTALLATION VIDEOS

[RMQ Flat Design](#)

MCAD MODEL

[einbautab_gr2](#)

[einbautab_gr2.stp](#)

MULTIMEDIA

[MCI Multicolor Light Indicator M22 with SmartWire-DT](#)

[easyE4 SmartWire-DT module with Remote Touch Display and RMQ multi color indicator](#)

[MCI MultiColor Light Indicator RMQ compact solution](#)

[RMQ small E-Stop emergency-stop button](#)

SALES NOTES

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

[eaton-control circuit-
devices rmq-titan-
fl144090en-en-us.pdf](#)

[eaton-rmq-flat-enclosure-
flyer-fl047003en-en-us.pdf](#)

[eaton-rmq-small-e-stop-
flyer-fl047006en-en-us.pdf](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

