


Power Supplies Data Sheet

Single, Dual, Triple and Quad Output

Broad Product Range

Current: Up to 6 Amps
Voltage: Up to 64 Volts
Power: Up to 217 Watts



Tools for Improved Debugging

- Models with from 1 to 4 outputs. ✔ Flexible choice of outputs to meet your DUT needs.
- Fully programmable via USB, RS-232, LAN and Ext I/O. ✔ Full remote control extends the usability from the bench to automated systems.
- Cutting edge DC Power Supply Design. Ripple & Noise $\leq 350 \mu\text{V}$, transient recovery time $\leq 50 \mu\text{s}$. ✔ Improved power supply specifications meets your low noise power needs.
- Ch1 and Ch2 support Constant Voltage and Constant Current Operation. ✔ Flexible voltage and current output configurations for a broader application coverage.
- Ch1 and Ch2 support Electronic Load functionality as CV, CC or CR. ✔ Use for charge/discharge testing (e.g. batteries) without the need for an Electronic Load.
- Only 213 mm Wide x 145 mm High x 312 mm Deep. Weight Approx. 7.5 kg. ✔ High power/high performance whilst take up the minimum of bench space.

Models and Characteristics

T3PS13206P	Ch1	0–32 V / 0–6 A	No C.V. or C.C. Mode
T3PS23203P	Ch1 / Ch2	0–32 V / 0–3 A	Support for C.V. and C.C. Modes
T3PS33203P	Ch1 / Ch2	0–32 V / 0–3 A	Ch1 / Ch2 support for C.V. and C.C. Modes
	Ch3	1.8 V / 2.5 V / 3.3 V / 5 V / 0–5 A	
T3PS43203P	Ch1 / Ch2	0–32 V / 0–3 A	Ch1 / Ch2 support for C.V. and C.C. Modes
	Ch3	0–5 V / 0–1 A	
	Ch4	0–15 V / 0–1 A	

MULTI-OUTPUT PROGRAMMABLE DC POWER SUPPLY



Front Panel



Rear Panel

T3X3200P Series

- 4.3" TFT LCD Display
- Supports Setting Value, Measurement Value and Output Waveform Display
- Load Function (CC, CV, CR Mode)
- Setting Resolution: 1 mV/0.1 mA; Read Back Resolution: 0.1 mV/0.1 mA
- Low Ripple Noise: $\leq 350 \mu\text{Vrms} / \leq 2 \text{ mArms}$
- Transient Response Time: $\leq 50 \text{ ms}$
- Utilizing Hardware to Realize Over Voltage Protection/ Over Current Protection/ Over Temperature Protection
- Delay Function/ Output Monitoring Function/ Output Recorder Function
- Intelligent Temperature Control Fan Effectively Reduces Noise
- Sequential Output Function and Built-in 8 Template Waveforms
- The Output Recorder Function Records The Output Voltage & Current Parameters with A Minimum Recording Interval of 1 Second
- Provides 10 Sets of Memory for Each Sequence/Delay/Recorder/ Panel Setting Condition
- T3PS33203P Supports A USB (Type A) Output Terminal
- Standard: RS-232, USB, Ext I/O; LAN

With the maximum output power of 217 W, the T3X3200P Series, the multi-channel programmable DC power supply, includes four models: T3PS13206P (0~32 V/0~6 A) for single-channel output, T3PS23203P for dual-channel output (CH1: 0~32 V/0~3 A, CH2: 0~32 V/0~3 A), T3PS33203P for three-channel output (Ch1: 0~32 V/0~3 A, CH2: 0~32 V/0~3 A, CH3: 1.8 V, 2.5 V, 3.3 V, 5.0 V/5 A) and T3PS43203P for four-channel output (CH1: 0~32 V/0~3 A, CH2: 0~32 V/0~3 A, CH3: 0~5 V/0~1 A, CH4: 0~15 V/0~1 A).

This series not only provides high program resolution (1 mV/0.1 mA) and read back resolution (0.1 mV/0.1 mA), but also features optimal low-ripple noise characteristics $\leq 350 \mu\text{Vrms} / \leq 2 \text{ mArms}$ and output transient recovery capability $\leq 50 \mu\text{s}$. Independent output on-off switch is provided for each channel.

For series and parallel applications of CH1 and CH2, the tracking function of the T3X3200P Series utilizes the internal circuit to automatically switch the output to serial or parallel output without additional external wiring,

providing users with convenience not only in operating procedures but also a more stable output. The tracking function design of other brands requires additional external wiring connections for the output in series or parallel. However, excessively long, thin or inconsistent external wiring may cause inaccurate voltage or current output.

The T3X3200P Series offers a variety of display modes, including single or multi-channel setting values, measurement values, and waveform displays. The Monitor function of the T3X3200P Series allows users to set monitoring conditions according to requirements, sound alarms or stop output during the measurement process, and stop measurement and protect the customer's DUT. The T3X3200P Series provides output recorder function, which records the voltage/current of the output process to the internal memory, and the result can be stored as a (*.REC) or (*.CSV) file, which can then be transferred to the USB flash drive and be exported to the PC for PC software or Excel to conduct future analysis.

The CH1/CH2 of the T3X3200P Series are designed with the load function. A single power supply can set one channel as the power output, and one channel for the load function to consume the power of the DUT to meet the basic charging and discharging test requirements for battery. Channel 1 and channel 2 not only provide 32 V/3 A power output, but also feature built-in maximum 32 V constant voltage load (CV), maximum 3.2 A constant current load (CC) and maximum 1 kΩ constant resistance load (CR) function.

The T3X3200P Series provides the sequential output function on Channel 1 and Channel 2. This function not only allows users to edit the power output waveform, but also allows users to set the sequential constant voltage (CV) or constant current (CC) load waveform, i.e. a serial power output or a simulation test of a dynamic load. In order to simplify the setting of waveform editing, the T3X3200P Series has 8 built-in template waveforms in the sequence output function for users to directly apply for output, including Sine, Pulse, Ramp, Stair Up, Stair Dn, Stair UpDn, Exp Rise, Exp Fall waveforms.

The internal protection functions include OVP/OCP/OPP/OTP, in which the protection mechanism for OVP/OCP/OTP is implemented by hardware circuit that has the advantage of faster response time compared with competitors who adopt software to achieve protections.

The OVP/OCP functions allow users to set the protection action point (except CH3 of T3PS33203P) according to the conditions of the DUT. The OPP is only activated during the operation of the load function. The Delay Function sets the length of time during channel 1 or channel 2 power output on or during power output off.

In addition, the Trigger In/Trigger Out functions synchronize external devices. The T3PS33203P channel 3 adds a 3 A USB (Type A) output terminal for USB charging test. The intelligent temperature controlled fan can adjust the speed according to the temperature of the power transistor so as to reduce unnecessary noise. The output value setting and the Sequence/Delay/Recorder functions provide 10 sets of internal memory for use, and can be loaded/stored using a USB flash drive. In addition to the standard RS-232 and USB remote interfaces, the T3X3200P Series also has LAN interface to facilitate different requirements. The commands of the T3X3200P Series conform to SCPI requirements.

APPLICATIONS

- School and Research Institute
- Energy Storage Device Industry
- Semiconductor Industry
- Consumer Electronics Industry

Ordering Information

Model	T3PS13206P (32 V/6 A) Single-Output Programmable DC Power Supply
	T3PS23203P (32 V/3 A*2) Dual-Output Programmable DC Power Supply
	T3PS33203P (32 V/3 A*2; 1.8 V or 2.5 V or 3.3 V or 5 V/5 A*1) Three-Output Programmable DC Power Supply
	T3PS43203P (32 V/3 A*2; 5 V/1 A; 15 V/1 A) Four-Output Programmable DC Power Supply
Accessories	Quick Start Guide x 1, Power cord x 3
	T3PS13206P Test Lead GTL-104 A x 1, GTL-105 A x 1
	T3PS23203P Test Lead GTL-104 A x 2
	T3PS33203P Test Lead GTL-104 A x 3
	T3PS43203P Test Lead GTL-104 A x 2, GTL-105 A x 2

Warranty: 3 Years return to Teledyne LeCroy.

SPECIFICATIONS

Model	T3PS43203P				T3PS33203P			T3PS23203P		T3PS13206P
-------	------------	--	--	--	------------	--	--	------------	--	------------

Output Mode

Number of Channel	CH1	CH2	CH3	CH4	CH1	CH2	CH3	CH1	CH2	CH1
Voltage	0 ~ 32 V	0 ~ 32 V	0 ~ 5 V	0 ~ 15 V	0 ~ 32 V	0 ~ 32 V	1.8/2.5/ 3.3/5.0V	0 ~ 32 V	0 ~ 32 V	0 ~ 32 V
Current	0 ~ 3 A	0 ~ 3 A	0 ~ 1 A	0 ~ 1 A	0 ~ 3 A	0 ~ 3 A	5 A	0 ~ 3 A	0 ~ 3 A	0 ~ 6 A
Tracking Series Voltage	0 ~ 64 V		-		0 ~ 64 V		-	0 ~ 64 V		-
Tracking Parallel Current	0 ~ 6 A		-		0 ~ 6 A		-	0 ~ 6 A		-

Constant Voltage Operation

Line Regulation	≤ 0.01 % + 3 mV									
Load Regulation	≤ 0.01 % + 3 mV (rating current ≤ 3 A); ≤ 0.02 % + 5 mV (rating current > 3 A)									
Ripple & Noise (5 Hz ~ 1 MHz)	≤ 350 μVrms		≤ 1 mVrms		≤ 350 μVrms		≤ 2 mVrms	≤ 350 μVrms		≤ 500 μVrms
Recovery Time	≤ 50 μs		≤ 50 μs		≤ 50 μs		≤ 100 μs	≤ 50 μs		≤ 100 μs

Constant Current Operation

Line Regulation	≤ 0.2 % + 3 mA									
Load Regulation	≤ 0.2 % + 3 mA									
Ripple & Noise	≤ 2 mArms				≤ 2 mArms			≤ 2 mArms		≤ 4 mArms

Programming Resolution

Voltage	1 mV				1 mV			-	1 mV		1 mV
Current	0.1 mA				0.1 mA			-	0.1 mA		0.2 mA

Tracking Operation (CH1, CH2)

Tracking Error	≤ 0.1 % + 10 mV of Master (0 ~ 32 V, No Load, with Load add Load regulation ≤ 100 mV)									
Parallel Regulation	Line: ≤ 0.01 % + 3 mV Load: ≤ 0.01 % + 3 mV (rating current ≤ 3 A); ≤ 0.02 % + 5 mV (rating current > 3 A)									
Series Regulation	Line: ≤ 0.01 % + 5 mV Load: ≤ 100 mV									
Ripple & Noise	≤ 1 mVrms, 5 Hz ~ 1 MHz									

CH3 Operation For (T3PS33203P)

Output Voltage	1.8 V / 2.5 V / 3.3 V / 5.0 V, ± 5 %									
Output Current	5 A									
Line Regulation	≤ 3 mV									
Load Regulation	≤ 5 mV									
Ripple & Noise	2 mVrms (5 Hz ~ 1 MHz)									
Transient Recovery Time	100 μs									
USB Port Output	1.8 V / 2.5 V / 3.3 V / 5.0 V, ± 0.35 V, 3 A									

Meter

Voltage Resolution	0.1 mV				0.1 mV			-	0.1 mV		0.1 mV
Current Resolution	0.1 mA				0.1 mA			-	0.1 mA		0.2 mA
Setting Accuracy	≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)				≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)			-	≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)		≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)
Readback Accuracy	≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)				≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)			-	≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)		≤ ±(0.03 % + 10 mV) ≤ ±(0.30 % + 10 mA)

Model	T3PS43203P				T3PS33203P			T3PS23203P		T3PS13206P
-------	------------	--	--	--	------------	--	--	------------	--	------------

DC Load Characteristic

Number of Channel	CH1	CH2	CH3	CH4	CH1	CH2	CH3	CH1	CH2	CH1
Channel	2		–	CH4	2		–	2		1
Display Power	0 ~ 50.00 W		–		0 ~ 50.00 W		–	0 ~ 50.00 W		0 ~ 100.00 W
Display Voltage	1 ~ 33.00 V		–		1 ~ 33.00 V		–	1 ~ 33.00 V		1 ~ 33.00 V
Display Current	0 ~ 3.200 A		–		0 ~ 3.200 A		–	0 ~ 3.200 A		0 ~ 6.200 A
CV Mode Setting Range	1.500 V ~ 33.00 V		–		1.500 V ~ 33.00 V		–	1.500 V ~ 33.00 V		1.500 V ~ 33.00 V
Resolution	10 mV		–		10 mV		–	10 mV		10 mV
Set Accuracy	≤ 0.1 % + 30 mV		–		≤ 0.1 % + 30 mV		–	≤ 0.1 % + 30 mV		≤ 0.1 % + 30 mV
Read Accuracy	≤ 0.1 % + 30 mV		–		≤ 0.1 % + 30 mV		–	≤ 0.1 % + 30 mV		≤ 0.1 % + 30 mV
CC Mode Setting Range	0 ~ 3.200 A		–		0 ~ 3.200 A		–	0 ~ 3.200 A		0 ~ 6.200 A
Resolution	1 mA		–		1 mA		–	1 mA		1 mA
Set Accuracy	≤ 0.3 % + 10 mA		–		≤ 0.3 % + 10 mA		–	≤ 0.3 % + 10 mA		≤ 0.3 % + 10 mA
Read Accuracy	≤ 0.3 % + 10 mA		–		≤ 0.3 % + 10 mA		–	≤ 0.3 % + 10 mA		≤ 0.3 % + 10 mA
CR Mode Setting Range	1 ~ 1 kΩ		–		1 ~ 1 kΩ		–	1 ~ 1 kΩ		1 ~ 1 kΩ
Resolution	1 Ω		–		1 Ω		–	1 Ω		1 Ω
Set Accuracy	≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		–		≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		–	≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)
Read Accuracy	≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		–		≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		–	≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)		≤ 0.3 % + 1 Ω (Voltage ≥ 0.1 V, and current ≥ 0.1 A)

Insulation

Chassis and Terminal	20 MΩ or above (DC 500 V)
Chassis and AC Cord	30 MΩ or above (DC 500 V)

Environment Condition

Operation Temp	0 ~ 40 °C
Storage Temp	-10 ~ 70 °C
Operating Humidity	≤ 80 % RH
Storage Humidity	≤ 70 % RH

Other

Power Source	AC100 V/120 V/220 V/230 V ± 10 %, 50/60 Hz
Dimensions & Weight	213 (W) x 145 (H) x 312 (D) mm; Approx. 7.5 kg

Specifications subject to change without notice.

ABOUT TELEDYNE TEST TOOLS



Company Profile

Teledyne LeCroy is a leading provider of oscilloscopes, protocol analyzers and related test and measurement solutions that enable companies across a wide range of industries to design and test electronic devices of all types. Since our founding in 1964, we have focused on creating products that improve productivity by helping engineers resolve design issues faster and more effectively. Oscilloscopes are tools used by designers and engineers to measure and analyze complex electronic signals in order to develop high-performance systems and to validate electronic designs in order to improve time to market.

The Teledyne Test Tools brand extends the Teledyne LeCroy product portfolio with a comprehensive range of test equipment solutions. This new range of products delivers a broad range of quality test solutions that enable engineers to rapidly validate product and design and reduce time-to-market. Designers, engineers and educators rely on Teledyne Test Tools solutions to meet their most challenging needs for testing, education and electronics validation.

Location and Facilities

Headquartered in Chestnut Ridge, New York, Teledyne Test Tools and Teledyne LeCroy has sales, service and development subsidiaries in the US and throughout Europe and Asia. Teledyne Test Tools and Teledyne LeCroy products are employed across a wide variety of industries, including semiconductor, computer, consumer electronics, education, military/aerospace, automotive/industrial, and telecommunications.

Distributed by:

Teledyne LeCroy (US Headquarters)

700 Chestnut Ridge Road
Chestnut Ridge, NY. USA 10977-6499

Phone: 800-553-2769 or 845-425-2000
Fax Sales: 845-578-5985
Phone Support: 1-800-553-2769
Email Sales: contact.corp@teledynelecroy.com
Email Support: support@teledynelecroy.com
Web Site: <http://teledynelecroy.com/>

World wide support contacts can be found at:
<https://teledynelecroy.com/support/contact>

World wide instrument service can be found at:
<https://teledynelecroy.com/support/service.aspx>

RoHS and WEEE information can be found at:
<https://teledynelecroy.com/support/rohs.aspx>

Teledyne LeCroy (European Headquarters)

Teledyne LeCroy GmbH
Im Breitenspiel 11c
D-69126 Heidelberg, Germany

Phone: +49 6221 82700
Fax: +49 6221 834655
Phone Service: +49 6221 8270 85
Phone Support: +49 6221 8270 28
Email Sales: contact.gmbh@teledynelecroy.com
Email Service: service.gmbh@teledynelecroy.com
Email Support: tlc.t3.appsupport.eu@teledyne.com
Web Site: <http://teledynelecroy.com/>

teledynelecroy.com



© 2019 Teledyne Test Tools is a brand and trademark of Teledyne LeCroy Inc. All rights reserved. Specifications, prices, availability and delivery subject to change without notice. Product brand or brand names are trademarks or requested trademarks of their respective holders.

T3 stands for Teledyne Test Tools.

16aug19