

T496, Tantalum, MnO₂ Tantalum, Fused, 22 uF, 10%, 25 VDC, SMD, MnO₂, Molded, Fused, N/A, 800 mOhms, 7343, Height Max = 3.1mm



Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.8mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	446.84 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Supplier:	KEMET
Series:	T496
Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Description:	SMD, MnO ₂ , Molded, Fused
Features:	Integral Fuse
RoHS:	Yes
Termination:	Tin
Shelf Life:	156 Weeks
MSL:	1

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC (85C), 16.75 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85°C
Dissipation Factor:	6.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	800 mOhms (100kHz)
Ripple Current:	433 mAmps (100kHz 25C), 389.7 mAmps (85C), 173.2 mAmps (125C)
Leakage Current:	5.5 uA (5min 20C)