

A.440 AND A.340MT SERIES NON-VERNIER DRIVERS

DRIVERS DESIGNED FOR PRODUCTION APPLICATIONS

Same characteristics as A.400 and A.300MT

- No vernier adjustment, torque set with a torque-meter.
- Performance exceeds ISO 6789 requirements ($\pm 6\%$ of the preset value).
- Handle release when required torque is reached, prevents inadvertent overtightening.
- Automatic reset every 120°.

ISO 6789 Type II - Class D - Class F



"Non vernier" release type torque driver

A.440 - Micro-Tech® "Production" torque screwdriver



NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

- Class II type F (A.440 production).
- Screwdriver without vernier; this non graduated screwdriver is adjusted on a control bench.
- One-direction screwdriver, right-hand torquing.
- Female hex output for use with bits series 1 - 1/4".
- 1/4" drive on the handle for use with a ratchet handle type A.300PA.
- Supplied with adjustment key 4 mm.
- Supplied with calibration certificate and individual identification number.

	L [mm]	Torque N.m	$\Delta\Delta$ [g]
A.442	147	0,5 - 2,5	300
A.444	168	2 - 10	400

