



KILI - FLEX S3
Réf. : 16130



Suitable for :	Outside
Type :	Boots
Activity :	Construction / Environment / Oil and Gas
Upper :	Supple full leather water resistant for 4 hours
Lining :	
Tongue :	
Ankle protection :	
Fastening :	
Toe cap :	Ultralight and extra wide Composite toe cap 200 joules LIGHT SYSTEM®
Midsole :	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole :	Foamed PU, anatomical, antistatic and anti bacterial
Sole :	PU/TPU multi-hardness EXTREM 4 outsole, oil resistant FO, antistatic, HI-CI
Sole pattern :	Deep cleated sole pattern for better slip resistance on wet or icy grounds
Weight (Kg/pair) :	1.400
Colors :	Brown upper, outsole black/grey/silver cleats
Sizes :	38-48 (5-13)
Standard :	EN ISO 20345:2011 SRC
CE certificate of conformity N° :	0075/020/161/08/11/0463 ??? EXT 21/12/11
Special features :	Two loops for easy and fast boot pull-on
Special features 2 :	
Special features 3 :	

SPECIAL FEATURES

-  Integral 100% composite (Air System + Light System + Flex System)
-  Metal free, non magnetic
-  4-hour water absorption and penetration resistance test (WR)
-  EXTREM 4

G GENERAL FEATURES

	Antistatic properties (A)	100%	100%
	Heel energy absorption (E)	100%	100%
	Abrasion resistance	100%	100%
	Crampon sole	100%	100%
	Heat-insulated sole (HI)	100%	100%
	Cold-insulated sole (CI)	100%	100%
	200 joule extra-wide toecap	100%	100%
	Hyper-ventilated lining	100%	100%
	Perforation-resistance 1100 N (P)	100%	100%