

Features

- Suitable for print
- Good burning properties
- Impact resistant
- Food-safe
- Crystal clear
- Excellent vacuum forming properties
- Made entirely from virgin material.
- 100% recyclable
- PETG is food grade and very impact resistant. Fire properties: Many PETG versions comply with fire class B1 and can therefore be used in many places where high fire requirements are required. Think of trade fairs, indoor shopping centres and airports.

RS PRO Clear Gloss Polyethylene Terephthalate Glycol Sheet

L:1000MM x W:1000MM X T:1.8MM

RS Stock No: 0845426



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description***RS PRO Clear Gloss Polyethylene Terephthalate Glycol Sheet***

RS PRO Clear Gloss Polyethylene Terephthalate Glycol Sheet is in between Acrylic (PMMA) and Polycarbonate (PC) in terms of technical properties and price. The crystal-clear material has excellent vacuum forming properties and good impact resistance. Polyester can be printed without any problem with all known printing techniques, except for offset printing. PETG combines superior vacuum forming properties with excellent mechanical properties. With PETG it is possible to design and produce very complex transparent displays, shop fittings and high-quality machines.

Key Features:

- *At the end of its life, ECO PETG is 100% recyclable, meaning it can be processed back into new sheets or other plastic products rather than ending up in a landfill*
- *Producing recycled plastic is a lower-energy process than synthesizing new resins from basic chemicals.*

Applications:

- *Food and drink storage*
- *Retail stands and displays*
- *Point of sale*
- *Sign making*
- *Packaging*
- *Glazing*
- *Protective screens*

General Specifications

Material	PETG (Polyethylene Terephthalate Glycol)
Form	Sheet
Colour	Clear
Length	1000MM
Width	1000MM
Thickness	1.8MM

Plastic Sheets

Mechanical Specifications

Impact Strength	ISO 179 kJ/m2 (150x stronger than glass)
Light Transmittance	>84%
Density	1.27g/cm³
Max service temperature	65°C
Tensile Strength	>45 MPa
Estimated CO ₂ per KG	2.55 kg - 4.08 kg

Simular Products

RS Code	Form	Dimensions	Thickness
0845425	ECO Sheet	500MM x 500MM	3MM
0845427	Sheet	500MM x 500MM	1.8MM
0845428	ECO Sheet	1000MM x 1000MM	3MM