


4

3

2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J			B	REVISED PER ECR-10-007257	20APR2010	HMR



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1
推奨基板取付穴寸法 : コネクタ搭載面 (非累積公差)
PC基板厚 : 1.0~1.6±0.1

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: Pre-Tin COPPER ALLOY

- 2 FINISH (ALL OVER): NICKEL PL. 1.27μm MIN
- 3 FINISH (CONTACT AREA): AU PL. 0.38μm MIN AFTER 2
- 4 FINISH (CONTACT TAIL): TIN PL. 2μm MIN AFTER 2
- 5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

1. 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂 (94V-0)、色: 黒
コンタクト: 銅合金
リテンションレグ: 錫めっき済銅合金

- 2 めっき: 全面: Ni下地めっき 1.27μm 以上
- 3 めっき: 接触部: 2の上に金めっき 0.38μm 以上
- 4 めっき: コンタクト半田付部: 2の上に錫めっき 2μm 以上
- 5. 文字の形状、大きさ、および位置については、大略を示すものであり、
詳細を示すものではありません。

2	1	2.5	6.0	7.6	1-1871468-2
POS.	n	A	B	C	PART NO.

P/N 1-1871468-2
(2P:X-KEY)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: ㎜	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±3° 0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ± FINISH 仕上
----------------------	--

MATERIAL
材料

DWN 20JUN2005
M. MAEBASHI
CHK 20JUN2005
T. KUDO
APVD 31AUG2005
D. MITSUGI
PRODUCT SPEC
108-78268
APPLICATION SPEC
取付適用規格
114-5377
WEIGHT
CUSTOMER DRAWING

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan
NAME
DYNAMIC DI200S 2.5mm PITCH
HDR ASSY, V-TYPE
2 POS
SIZE
A300779
CAGE CODE
C-1871468
DRAWING NO
114-5377
RESTRICTED TO
SCALE
6:1
SHEET
1
OF
1
REV
B