

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Applicator for the efficient printing and application of movable E-WM... markers on wires and cables in a single automated process step

Product description

To achieve maximum efficiency in wire and cable identification processes, combine a standard roll printer from the THERMOMARK E SERIES with the THERMOMARK E.WIRE applicator. This provides you with an automated printing and application system that enables you to achieve time savings of up to 70% compared to manual identification processes. Use the THERMOMARK E.WIRE to create movable markers for all types of cylindrical objects as well as twisted wires. Thanks to their triangular shape, they can be marked on all three sides. In this process, the THERMOMARK E.WIRE automatically measures the diameter of the cylindrical object, cuts the ready-printed E-WM... marking foil in continuous format to the appropriate length, places this around the cylindrical object, and then seals the marker shut with a hot-sealed joint. This results in a captive marker that is optimally tailored to the diameter and can also move radially and axially. Thanks to this unique system, all diameters between 1.8 mm/0.07" and 5.6 mm/0.22" can be marked efficiently using just one type of material.

Scope of supply:

THERMOMARK E.WIRE, TM E.WIRE/E.SLEEVE-PR pressure roller (1259203), multilingual packing slip

Your advantages

- Maximum efficiency: time savings of up to 70% compared to manual printing and application processes
- Consistently high level of efficiency over the entire working day through intuitive handling, which helps reduce costs
- Planning accuracy with regard to productivity and quality: in the case of order peaks, productivity can be increased significantly using the same number of employees
- Reduction in the number of user errors through intuitive step-by-step guidance along the entire identification process as well as automatic data processing from CAE systems and other popular file formats for data exchange
- The continuous format means that one material can cover all wire and cable diameters ranging from 1.8 mm ... 5.6 mm (0.07" ... 0.22"). It is therefore not necessary to change materials
- Easy and efficient handling, as the diameter of the cylindrical object is measured automatically and the size of the marker is optimally adjusted accordingly
- Thanks to the three-sided printing and sliding action of the markers on the wires/cables, the marking is clearly visible once installed
- Due to the triangular shape of the markers, different information can be printed on each of the three marking areas
- The very strong heat-sealed joint ensures that the markers remain captive
- The permanent identification of single-core wires, wires, cables, twisted cable bundles, and other cylindrical objects provides maximum flexibility
- Thanks to the intuitive operating concept and symmetrical structure, the applicator can be used ergonomically by both right- and left-handed users
- Quick and easy mounting of the applicator on the roll printer via hexagon screw
- The applicator is connected via the D-SUB interface on the roll printer and is detected automatically by the software

Commercial data

THERMOMARK E.WIRE - Applicator



1203216

<https://www.phoenixcontact.com/gb/products/1203216>

Item number	1203216
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1222
Product key	BG122Z
GTIN	4063151268916
Weight per piece (including packing)	3,161 g
Weight per piece (excluding packing)	3,161 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK E.WIRE - Applicator



1203216

<https://www.phoenixcontact.com/gb/products/1203216>

Technical data

Product properties

Product type	Printing system accessories
--------------	-----------------------------

Electrical properties

Supply

Supply voltage range	24 V DC
----------------------	---------

Dimensions

Width	239 mm
Height	179 mm
Length	237 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
---------------------------------	----------------

THERMOMARK E.WIRE - Applicator



1203216

<https://www.phoenixcontact.com/gb/products/1203216>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1203216>



cULus Listed

Approval ID: E140403



cULus Listed

Approval ID: E140403

Classifications

ECLASS

ECLASS-13.0	19140192
-------------	----------

ETIM

ETIM 9.0	EC001675
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	05ba1772-0cf5-402d-a007-59ae94d24806