




Image may differ from product. See specification for details.



LAGH 400

Manual operated grease gun, one handed

The SKF Grease Gun LAGH 400 is ideal for usage in agricultural, industrial and construction industries and for private use. The grease gun is equipped with a filler nipple and air-release valve for easy re-filling by filler or grease pumps. It can also suitable for usage with grease cartridges. The ergonomic design for one handed operation, the flexible high

pressure hose and the possibility to mount the hose in both horizontal and vertical position makes this grease gun very versatile and easy to use.

- Easy to use with only one hand
- Refillable: grease filling nipple and de-airing valve allow filling up by filler or grease pumps
- Heavy duty: Operating pressure up to 300 bar (4 350 psi)
- Flexible hydraulic hose can be bent and mounted horizontally or vertically on the grease gun

Overview

Dimensions

| | |
|--------------------|----------|
| Reservoir volume | 500 ml |
| Filling connection | DIN 1283 |
| Length | 370 mm |

Performance

| | |
|-------------------|---------|
| Maximum pressure | 30 MPa |
| Maximum pressure | 300 bar |
| Volume per stroke | 0.46 ml |

Properties

| | |
|-----------------------------------|---|
| Recommended applications | For manual filling of greasing points in industrial, construction and agricultural applications |
| Grease supply | Loose or Cartridge |
| Use of standard grease cartridges | Yes, type DIN 1284 |
| NLGI class of lubricant (max) | 2 |
| Suitable for grease nipples | Standard nipples as per DIN 71412 |
| Operation | One handed |
| Pipe/Hose thread connection | M10x1 |
| Extension pipe | Optional |
| Hose | Yes, 300mm |

| | |
|---------------------------------------|----------------------------------|
| Can be filled with Grease filler pump | Yes, with SKF LAGF 18 or LAGF 50 |
|---------------------------------------|----------------------------------|

Logistics

| | |
|--------------------|-------------|
| Product net weight | 1.28 kg |
| eClass code | 23-06-91-06 |
| UNSPSC code | 15121902 |

Compatible products

Spare part

| | |
|---|-----------------------------|
| Spare nozzle for Manual operated grease gun | 1077600-1 A |
| Spare filling nipple for Manual operated grease gun | 1077600-3 |
| Spare pressure hose for grease gun | 1077601 |

Accessory

| | |
|------------------------------|---------------------------|
| Grease nipple set | LAGN 120 |
| Grease nozzle set | LAGS 8 |
| Grease fitting caps and tags | TLAC 50/B |
| Grease fitting caps and tags | TLAC 50/G |
| Grease fitting caps and tags | TLAC 50/R |
| Grease fitting caps and tags | TLAC 50/Y |
| Grease fitting caps and tags | TLAC 50/Z |
| Grease coupler | LAGC S |

Recommended product

| | |
|--|-----------------------------|
| Grease meter, measuring grease discharge | LAGM 1000E |
| Ultrasound lubrication checker | TLGU 10 |
| Grease filler pump for use on drums | LAGF 18 |
| Grease filler pump for use on drums | LAGF 50 |
| Manual operated grease gun | TLGH 1 |
| Manual operated grease gun | 1077600 |
| Manual operated grease gun | 1077600 H |
| Manual operated grease gun set | 1077600/SET |



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.