



2 YEARS
MANUFACTURER
GUARANTEE



Product number 1173750003
EAN 4007123684656

TECHNICAL DATA

Luminous flux	200 lm
Power consumption	5 W
Colour temperature	6800 K
Colour rendering index	70-79 (class 2 A)
Lifetime	50000 h
Battery capacity	0.6 Ah
Battery voltage	3.7 V

Light duration max.	13 h
Battery charging time approx.	1.5 h
Battery type	Special battery
Battery technology	Lithium-ion
Protection class	III
Degree of protection (IP)	IP44
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.05 kg
Dimension LxWxH (without packing)	1.6 cm x 2.2 cm x 14.9 cm

Weight of product (including packaging)	0.15 kg
Dimension LxWxH (incl. packing)	6.4 cm x 8.7 cm x 17 cm