Specifications



Head, Harmony XB5, black Ø 40 General safe stop Ø22 mm trigger and latching turn to release

Local distributor code: 409066263

ZB5AS842Y

EAN Code: 3606480611018

Main

Range of product	Harmony XB5	
Product or component type	Head	
Product destination	General safe stop push button	
Device short name	ZB5	
Bezel material	Dark grey plastic	
Head type	Standard	
Mounting diameter	22 mm	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	trigger action and mechanical latching	
Reset	Turn to release	
Operator profile	Black mushroom Ø 30 mm, unmarked	

Complementary

CAD overall width	30 mm	
CAD overall height	30 mm	
CAD overall depth	56 mm	
Net weight	0.05 kg	
Mechanical durability	300000 cycles	
Station name	XALD 15 cut-outs XALK 15 cut-outs	
Electrical composition code	C7 for <4 contacts using single blocks in front mounting C8 for <4 contacts using single and double blocks in front mounting C11 for <3 contacts using single blocks in front mounting C15 for <1 contacts using single blocks in front mounting SF1 for <3 contacts using single blocks in rear mounting C10 for <4 contacts using single and double blocks in front mounting	
Compatibility code	ZB5	

Environment

Protective treatment	тн
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
Overvoltage category	Class II conforming to IEC 60536

IP degree of protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K	
NEMA degree of protection	NEMA 13 NEMA 4X	
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m	
IK degree of protection	IK03 conforming to IEC 50102	
Standards	UL 508 IEC 60364-5-53 JIS C8201-5-1 CSA C22.2 No 14 GB 14048.5 JIS C8201-1	
Product certifications	LROS (Lloyds register of shipping) UL listed BV CSA	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	5.2 cm
Package 1 Length	4.2 cm
Package 1 Weight	42.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.813 kg

Logistical informations

Country of origin

CZ

Contractual warranty

Warranty

18 months

🜔 Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

1

Environmental Data explained >

How we assess product sustainability >

earrow Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)

Environmental Disclosure

Product Environmental Profile

Use Better

Materials and Substances		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	

Use Again

\odot Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No