

Technical data

4T-2687/2631

Single row tapered roller bearings




Tapered roller bearing, pressed steel cage

KIT CONTENT


4T-2631, 4T-2687

VISUAL (S)



4T-2687/2631

Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	25,4 mm
D - External diameter	66,421 mm
B - Bearing/Inner ring width	25,433 mm
C - Outer ring width	19,05 mm
T - Total width	23,812 mm
d1 - External diameter inner ring	45 mm
a - Charge load application point	14,512 mm
Mass	0,444 kg

PRODUCT PERFORMANCE	
C - Dynamic load	71,5 kN
C0 - Static load	72,5 kN
Cu - Fatigue limit load	8,8 kN

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.25
Y0 - Static axial load coefficient	1.3
Y2 - Upper axial load coefficient	2.36
N lim - Oil lubrication limit speed	8200 tr/min
N lim - Grease lubrication limit speed	6200 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	31,5 mm
db min - Min IR shoulder diameter	33,5 mm
Da max - Max shoulder diameter OR	58 mm
Db min - Min OR shoulder diameter	60 mm
ra max - Max fillet radius	1,3 mm
r1a - Max fillet radius	1,3 mm

KIT COMPONENT

Cone designation	4T-2687
Cup designation	4T-2631

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-2687/2631
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material

Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X_o	Y_o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

