

SUBMINIATURE SOLID STATE LAMP

Blue

Part Number: KM2520QBC-G09



ATTENTION OBSERVE PRECAUTIONS FOR HANDLING **ELECTROSTATIC** DISCHARGE **SENSITIVE** DEVICES

Features

- Subminiature package.
- Z-bend lead.
- Long life solid state reliability.
- Low package profile.
- Moisture sensitivity level : level 3.
- Package: 1000pcs / reel.
- · RoHS compliant.

Description


The Blue source color devices are made with InGaN Light Emitting Diode.

Static electricity and surge damage the LEDS.


It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.


All devices, equipment and machinery must be electrically grounded.

Package Dimensions









Notes:

- All dimensions are in millimeters (inches).
 Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- 5. The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAJ9588 REV NO: V.5B DATE: MAR/30/2013 PAGE: 1 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1202002380

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
		, , , , , , , , , , , , , , , , , , ,	Min.	Тур.	201/2
KM2520QBC-G09	Blue (InGaN)	Water Clear	700	1300	20°

Notes:

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value. 2. Luminous intensity/ luminous Flux: +/-15%.
- 3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	461	10	nm	IF=20mA
λD [1]	Dominant Wavelength	Blue	465		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Blue	25		nm	IF=20mA
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Blue	3.3	4	V	IF=20mA
lr	Reverse Current	Blue		50	uA	V _R =5V

Notes:

- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.


Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Units	
Power dissipation	120	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	150	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		


Note:


1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAJ9588 **REV NO: V.5B DATE: MAR/30/2013** PAGE: 2 OF 5 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1202002380





Blue KM2520QBC-G09











SPATIAL DISTRIBUTION


 SPEC NO: DSAJ9588
 REV NO: V.5B
 DATE: MAR/30/2013
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1202002380

KM2520QBC-G09

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

 1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


 3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



Tape Dimensions (Units: mm)

Reel Dimension







SPEC NO: DSAJ9588 **REV NO: V.5B DATE: MAR/30/2013** PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1202002380

PACKING & LABEL SPECIFICATIONS

KM2520QBC-G09







Detailed application notes are listed on our website. http://www.kingbright.com/application_notes

SPEC NO: DSAJ9588 APPROVED: WYNEC REV NO: V.5B CHECKED: Allen Liu DATE: MAR/30/2013 DRAWN: Y.Liu PAGE: 5 OF 5 ERP: 1202002380