




tested to work



## 19335-231 Winter Jacket

breathable - wind- and waterproof - CLIMASCOT®-lining - two-toned

MASCOT® ACCELERATE SAFE



100% polyester

210 g/m²



Ripstop. Shrinkage max. 2%. The product is according to EN ISO 20471 certified to retain its qualities with 50 domestic washes. Hydrostatic pressure test > 10,000 mmH<sup>2</sup>O according to EN ISO 811.

**Industrial care category C2**



- Breathable, wind and waterproof with taped seams.
- Unique CLIMASCOT® insulation provides warmth without bulk. Lightweight, soft CLIMASCOT® insulation takes up almost no space when compressed.
- Chest pocket with waterproof zip.
- Front pockets with waterproof zips.
- Flap on back of jacket can be folded up for standard back length or released for extended back.

### Technical info

Fluorescent and with vertical and oblique, transverse reflective strips. The fabric is highly durable, breathable, wind and waterproof. CLIMASCOT® Lightweight Insulation. Two-toned. Taped seams. Detachable lined hood with adjustable drawstring. Fastening with waterproof zip and double storm flap. Inner pocket - two with zips and one open mesh. Detachable ID card holder. Chest pocket with waterproof zip. Front pockets with waterproof zips. High collar. Rib inside the bottom trim on the front of the jacket. Flap on back of jacket can be folded up for standard back length or released for extended back. Rib (hidden in storm flap) at cuffs. Hook and loop band fastening at cuffs. Zip at lower back for logo printing/ embroidery. With print effects.

### User



**CLIMASCOT®**  
Lightweight insulation

### Certifications



EN ISO 20471



EN ISO 20471



EN 342



EN 343



HIGH-VIS



### Logo

You should choose a transfer that can be heated at a maximum of 145 degrees with consideration to print on the product. Remember to check the washing instructions for the chosen transfer before washing the product.

The product is certified with maximum (M-5XL) 0,0200 m<sup>2</sup> (S) 0,2500m<sup>2</sup> logo area. This approved area must not be exceeded. Logo on, respectively, front or back of the product can constitute only a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

### Logo placement:

- Workwear logo stretch. Over left breast pocket. Max 9x3 cm/3.5x1.1 inches
- Workwear logo stretch. Right breast pocket. Max 8x7 cm/3.1x2.7 inch
- Workwear logo stretch. Mid-back. Max 20x20 cm/7.8x7.8 inches
- Workwear logo stretch. Horizontal on right sleeve. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Special placement. Contact to