




## 160 Watt Low Cost Open Frame Power Supply PSA160U 1U Switching Power Supply for IT Solutions



### Features

- 2" x 4" footprint
- Class B EMI
- Fits 1U height requirements
- OCP, OVP and Short Circuit Protection

### Applications

- IT Equipment
- Cable TV
- Networking Equipment
- Multimedia Equipment

### Safety Approvals

- CE
- cUL/UL

### Mechanical Characteristics <sup>(1)</sup>

- Length: 101.6mm (4in)
- Width: 50.8mm (2in)
- Height: 34.5mm (1.36in)
- Weight: 184-195g (6.49-6.88oz)

### Output Specifications

Model	DC Output Voltage	Load		Ripple P-P (max.)	Regulation		Max Power <sup>(3)</sup>
		Min.	Max. <sup>(2)</sup>		Line	Load	
PSA160-210-R	12V	50mA	13.34A	200mV	±5%		159.6W
	12V-fan	50mA	0.4A		+30%	-20%	4.8W
PSA160-212-R	24V	50mA	6.67A	270mV	±5%		160.1W
	12V-fan	50mA	0.4A		+30%	-20%	4.8W
PSA160-218-R	48V	50mA	3.34A	400mV	±5%		160.3W
	12V-fan	50mA	0.4A		+30%	-20%	4.8W
PSA160-216-R	56V	50mA	2.86A	480mV	±5%		160.2W
	12V-fan	50mA	0.4A		+30%	-20%	4.8W

Notes (1) – 12V model has a weight of 184g, while all other models weigh 195g

Notes (2) – CFM forced air required, load drops to 56.3% of maximum without fan

Notes (3) – CFM forced air required for full power – 90W without fan

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at [www.phihong.com](http://www.phihong.com) for the most up-to-date specifications and contact information.

**INPUT:****AC Input Range**

90 to 264VAC

**AC Input Rating**

100 to 240VAC

**AC Input Frequency**

47-63Hz

**AC Input Current**

2.2A (RMS) maximum at 115VAC

1.2A (RMS) maximum at 230VAC

**AC Inrush Current**

40A maximum at 115VAC

70A maximum at 230VAC

**Leakage Current**

1mA maximum

**OUTPUT:****Output Power**

160W with fan

90W without fan

4.8W – Fan output

**Efficiency (at full power)**

86-88% at 115VAC

88-90% at 230VAC

**ENVIRONMENTAL:**

Operating temperature -20°C to 70°C

Storage Temperature -40°C to 85°C

Humidity 20 to 90% RH

**Cooling**

12.6 CFM for full power

w/ fan - 160W, 100% load at maximum 45°C

w/o fan – 90W, 56.3% load with 35°C

**EMC**

EN55022 Class B

**EMI**

EN61000-4-2

EN61000-4-3

EN61000-4-4

EN61000-4-5

EN61000-4-6

EN61000-4-100

EN61000-4-11

EN61000-3-2 Class D

EN61000-3-3

**Dielectric Withstand (HI-POT) Test**

Primary to Secondary: 3000VAC for 1 minute

Primary to Ground: 1500VAC for 1 minute

**Insulation Resistance:**

Primary to Secondary: &gt;7M ohm 500VDC

**Over-Voltage Protection**

135% maximum

**Over Current Protection**

105~150%, Auto recovery

**Short Circuit Protection**

Output can be shorted permanently without damage

**AC Input Connector**

3 Pin 3.96mm, PIN 2 N.C.

**DC Output Connector**

8 Pin 3.96mm

**Fan Output Connector**

2 Pin 2.00mm

